



Product: [2132A](#)

Fieldbus, 16 Pr #16 Str TC, XLPE Ins, IS/OS, TPE Jkt, 600V TC-ER

[Request Sample](#)

Product Description

Fieldbus, 16 Pair 16AWG (7x24) Tinned Copper, XLPE Insulation, Individual & Overall Beldfoil® Shield, TPE Outer Jacket, 600V TC-ER

Technical Specifications

Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	16	16 AWG	7x24	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code
Pair(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.038 in (0.97 mm)	Blue, Orange and Numbered

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC	Individually Shielded

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	16 AWG (7x24) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
TPE - Thermoplastic Elastomer	0.085 in (2.2 mm)	1.321 in (33.55 mm)	Yes

Overall Cable Diameter (Nominal):	1.321 in (33.55 mm)
-----------------------------------	---------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Capacitance Unbalance	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
4.2 Ohm/1000ft (14 Ohm/km)	1.2 pF/ft (3.9 pF/m)	22 pF/ft (72 pF/m)	100 Ohm	64%	7.2 Amps per Conductor

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss (Attenuation)
0.039	0.065 dB/100ft

High Frequency

Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
0.091 dB/100ft	100 Ohm

Voltage

UL Voltage Rating

600 V (TC-ER), 600 V (CSA CIC Type TC)

Mechanical Characteristics**Temperature**

UL Temperature	Operating
90°C Wet/Dry	-40°C to 90°C

Table Notes:	-40C
Max. Pull Tension:	1536 lbs (696.7 kg)
Bulk Cable Weight:	847 lbs/1000ft (1260 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Flammability / Reaction to Fire:	UL 1581 Vertical Tray, FT4, IEC 60332-3-24
NEC / UL Compliance:	Article 336, TC-ER
AWM Compliance:	AWM I A/B II A/B
CEC / C(UL) Compliance:	CIC, TC
ISO/IEC Compliance:	IEC 61158-2
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ISA/SP-50 Type A

History

Update and Revision:	Revision Number: 0.388 Revision Date: 11-09-2022
----------------------	--

Part Numbers**Variants**

Item #	Color	Putup Type	Length	UPC
2132A 0061000	Blue, Light	Reel	1,000 ft	612825130321
2132A 0031000	Orange	Reel	1,000 ft	612825130314

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.