



Part Number: 2146A

Category 6 Indoor/Outdoor CMR/CMX Cable

Product Description

CAT6 (350MHz), 4-Pair, U/UTP-Unshielded, Riser-CMR, CMX Outdoor, Premise Horizontal Cable, 23 AWG solid bare copper conductors, non-plenum, Polyolefin insulation, Film separator, Ripcord, UV Resistant PVC Jacket

Technical Specifications

Product Overview

Environmental Space:	Indoor/Outdoor
Suitable Applications:	Premise Horizontal Cable, Outdoor, Riser, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Outer Jacket Material

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.255 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
78 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	17 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	35 ns/100m	68 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.0 dB/100m	75.3 dB	75.3 dB	73.3 dB	73.3 dB	70.8 dB	67.8 dB	20.0 dB	100 +/- 15	40.0 dB	35.0 dB
4 MHz	3.7 dB/100m	66.3 dB	66.3 dB	62.5 dB	62.5 dB	58.8 dB	55.8 dB	23.0 dB	100 +/- 15	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	61.8 dB	61.8 dB	56.5 dB	56.5 dB	52.7 dB	49.7 dB	24.5 dB	100 +/- 15	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	60.3 dB	60.3 dB	54.4 dB	54.4 dB	50.8 dB	47.8 dB	25.0 dB	100 +/- 15	40.0 dB	15.0 dB
16 MHz	7.4 dB/100m	57.2 dB	57.2 dB	49.8 dB	49.8 dB	46.7 dB	43.7 dB	25.0 dB	100 +/- 15	38.0 dB	10.9 dB
20 MHz	8.3 dB/100m	55.8 dB	55.8 dB	47.4 dB	47.4 dB	44.8 dB	41.8 dB	25.0 dB	100 +/- 15	37.0 dB	9.0 dB
25 MHz	9.4 dB/100m	54.3 dB	54.3 dB	45.0 dB	45.0 dB	42.8 dB	39.8 dB	24.3 dB	100 +/- 15	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	52.9 dB	52.9 dB	42.4 dB	42.4 dB	40.9 dB	37.9 dB	23.6 dB	100 +/- 15	35.1 dB	5.1 dB
62.5 MHz	15.1 dB/100m	48.4 dB	48.4 dB	33.3 dB	33.3 dB	34.9 dB	31.9 dB	21.5 dB	100 +/- 15	32.0 dB	
100 MHz	19.3 dB/100m	45.3 dB	45.3 dB	26.0 dB	26.0 dB	30.8 dB	27.8 dB	20.8 dB	100 +/- 15	30.0 dB	
155 MHz	24.5 dB/100m	42.4 dB	42.4 dB	17.9 dB	17.9 dB	27.0 dB	24.0 dB	19.5 dB	100 +/- 22	28.1 dB	
200 MHz	28.2 dB/100m	40.8 dB	40.8 dB	12.6 dB	12.6 dB	24.8 dB	21.8 dB	18.7 dB	100 +/- 22	27.0 dB	
250 MHz	31.8 dB/100m	39.3 dB	39.3 dB	7.5 dB	7.5 dB	22.8 dB	19.8 dB	18.0 dB	100 +/- 32	26.0 dB	
300 MHz	35.2 dB/100m	38.1 dB	36.1 dB	2.9 dB	0.9 dB	21.3 dB	18.3 dB	17.5 dB	100 +/- 32	25.2 dB	
350 MHz	38.4 dB/100m	37.1 dB	35.1 dB			19.9 dB	16.9 dB	17.0 dB	100 +/- 32	24.6 dB	
400 MHz	41.5 dB/100m	36.3 dB	34.3 dB			18.8 dB	15.8 dB	16.6 dB	100 +/- 32	24.0 dB	
450 MHz	44.3 dB/100m	35.5 dB	33.5 dB			17.7 dB	14.7 dB	16.2 dB	100 +/- 32	23.5 dB	
500 MHz	47.1 dB/100m	34.8 dB	32.8 dB			16.8 dB	13.8 dB	15.9 dB	100 +/- 32	23.0 dB	
550 MHz	49.7 dB/100m	34.2 dB	32.2 dB			16.0 dB	13.0 dB	15.6 dB	100 +/- 32		

Segregation class according EN50174-2: a

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Installation Temp Range:	-20°C To +75°C
UL Temp Rating:	90°C
Storage Temp Range:	-40°C To +75°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Cold Bend Test:	-40°C Compliance Per UL 1581
Bulk Cable Weight:	29 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius During Installation:	2.75 in
Min Bend Radius/Minor Axis:	1.0 in

Standards

NEC/(UL) Specification:	CMG, CMR, CMX-Outdoor
CEC/C(UL) Specification:	CMR-CMX OUTDOOR OR CMG
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Fca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Specification:	Outdoor Use ANSI/ICEA S56434, ANSI/ICEA S99689, Broadband Outdoor Use ANSI/ICEA S-99-689, Indoor/Outdoor Use ANSI/ICEA S100685
Third Party Performance Verification:	Category 6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes

EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL 1666 Riser
CSA Flammability:	FT4
ISO/IEC Flammability:	60332-1
IEEE Flammability:	1202 Vertical Tray
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	2413

Part Number

Non-Plenum Number:	2412
--------------------	------

Variants

Item #	Color	UPC
2146A 0101000	Black	612825062264

Patent:	https://www.belden.com/resources/patents
---------	---

Product Notes

Notes:	Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

History

Update and Revision:	Revision Number: 0.210 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.