Belden



Product: 21529

TC-CIC 600V, 31 C #14 Str BC, XLPE Ins, Blk PVC Jkt, 90C Dry/Wet CSA HL SUN RES DIR BUR

Product Description

CSA Tray TC-CIC 600V, 31 Conductor 14AWG (7x22) Bare Copper, XLPE Insulation, Black PVC Outer Jacket, 90C Dry/Wet CSA HL SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications:	CEC Power and Control Applications

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	31	14	7x22	BC - Bare Copper
Ground Wire	1	14 AWG	7x22	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLP, XLPO, XLPE (Thermoset)	0.032 in (0.81 mm)	0.135 in (3.43 mm)	Black and Numbered
Ground Wire	XLP, XLPO, XLPE (Thermoset)		0.132 in (3.35 mm)	Green

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.095 in (2.4 mm)	1.074 in (27.28 mm)	Yes

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	2.68 Ohm/1000ft (8.79 Ohm/km)	17.5 Amps per Conductor at 30°C
Ground Wire		

Voltage

Voltage Rating
600 V (CSA TC)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation
90°C Dry, 90°C Wet	Wet/Dry: -40°C to 90°C	-25°C To +90°C

Bend Radius

Installation Min.

6.44 in (164 mm)

Max. Pull Tension:	1474 lbs (668.6 kg)
Bulk Cable Weight:	795 lbs/1000ft (1180 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, UV Resistance, Burial
AWM Compliance:	C22.2#230 Type TC, C22.2#239 Type CIC
CEC / C(UL) Compliance:	TC, CIC
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.50 Revision Date: 10-07-2026

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.