



Product: [2157AA](#)

Nurse Call System, ASCOM Telligence, 2 Pair 16 AWG, CMR

Product Description

Commercial Audio Cable, 2 pair 16 AWG stranded bare copper conductors with polyolefin insulation, PVC jacket with ripcord, CMR rated.

Technical Specifications

Product Overview

Suitable Applications:	Nurse Call System
------------------------	-------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
16	19x29	BC - Bare Copper	2

Conductor Count:	2
------------------	---

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.008 in

Color Chart

Number
Black
Red

Outer Shield Material

Material
No Shield

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.180 in	0.017 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
4.2 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
23 pF/ft

Inductance

Nominal Inductance
0.14 μ H/ft

Current

Max. Recommended Current [A]

6.25 Amps per Conductor at 25°C

Voltage**UL Voltage Rating**

300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	23 lbs/1000ft
Max. Pull Tension:	59 lbs
Min. Bend Radius/Minor Axis:	1.75 in

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Vertical Riser

Plenum/Non-Plenum

Plenum (Y/N):	N
Plenum Number:	2157PA

Part Number**Variants**

Item #	Color	Put-Up Type	Length	UPC
2157AA T32U1000	Green, Signal	UnReel	1,000 ft	612825130604

History

Update and Revision:	Revision Number: 0.60 Revision Date: 08-27-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.