



Part Number: 2112A

Fieldbus, 8 Pr #16 Str TC, XLPO Ins, IS/OS, TPE Jkt, CMG

[🛒 Request Sample](#)

Product Description

Fieldbus, 8 Pair 16AWG (7x24H) Tinned Copper, XLPO Insulation, Individual & Overall Beldfoil® Shield, Orange TPE Outer Jacket, CMG

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
16	7x24	TC - Tinned Copper	8

Conductor Count: 16

Insulation

Material	Nominal Wall Thickness
XLP - Cross Linked Polyolefin	0.038 in

Color Chart

Number	Color
1	Blue and Orange Numbered 1
2	Blue and Orange Numbered 2
3	Blue and Orange Numbered 3
4	Blue and Orange Numbered 4
5	Blue and Orange Numbered 5
6	Blue and Orange Numbered 6
7	Blue and Orange Numbered 7
8	Blue and Orange Numbered 8

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	18	7x26

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	16	7x24 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
TPE - Thermoplastic Elastomer	0.982 in	0.085 in	Yes

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
4.2 Ohm/1000ft

Capacitance

Max. Capacitance Unbalance	Nom. Capacitance Conductor to Conductor

1.2 pF/ft	22 pF/ft
-----------	----------

Inductance

Nominal Inductance
0.22 µH/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.039 MHz	0.065 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]
64 %

High Freq

Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
0.091 dB/100ft	100 Ohm

Current

Element	Max. Recommended Current [A]
Per Conductor	10.1 Amps per Conductor

Voltage

Description	UL Voltage Rating
CSA CIC type TC	300 V RMS

Electrical Characteristics Notes:	Max Propagation Delay Change From 7.812 kHz to 39.06 kHz: 518 pS/ft
Other Electrical Characteristic 2:	31.25 KBits/sec

Temperature Range

Installation Temp Rating:	-25°C
UL Temp Rating:	90°C
Operating Temp Range:	-40°C To 90°C

Mechanical Characteristics

Oil Resistance:	Yes
Bulk Cable Weight:	478 lbs/1000ft
Max Recommended Pulling Tension:	786 lbs
Min Bend Radius/Minor Axis:	10 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG, ITC, PLTC-ER
CEC/C(UL) Specification:	CIC, TC
CSA AWM Specification:	AWM I A/B II A/B

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	60332-3-24 (Category C)
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length
2112A 0061000	Blue, Light	612825129318	1,000 ft
2112A 0065000	Blue, Light	612825129325	5,000 ft
2112A 0031000	Orange	612825129295	1,000 ft
2112A 0035000	Orange	612825129301	5,000 ft

History

Update and Revision:	Revision Number: 0.347 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.