



Product: [2128A](#)

Fieldbus, 2 Pr #16 Str TC, XLPE Ins, IS/OS, TPE Jkt, 600V TC-ER

[Request Sample](#)

Product Description

Fieldbus, 2 Pair 16AWG (7x24) Tinned Copper, XLPE Insulation, Individual & Overall Beldfoil® Shield, TPE Outer Jacket, 600V TC-ER

Technical Specifications

Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Pair(s)	2	16	7x24	TC - Tinned Copper

Insulation

Element	Material	Thickness	Color Code
Pair(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.038 in	Blue, Orange and Numbered

Inner Shield Material

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC	Individually Shielded

Outer Shield Material

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	16 AWG (7x24) TC

Outer Jacket Material

Material	Thickness	Nom. Diameter	Ripcord
TPE - Thermoplastic Elastomer	0.063 in	0.629 in	Yes

Cable Diameter (Nominal):	0.629 in
---------------------------	----------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Capacitance Unbalance	Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
4.2 Ohm/1000ft	22 pF/ft	1.2 pF/ft	100 Ohm	64%	11.6 Amps per Conductor

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.039 MHz	0.065 dB/100ft

High Freq

Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
0.091 dB/100ft	100 Ohm

Voltage

UL Voltage Rating

600 V (TC-ER), 600 V (CSA CIC Type TC)

Mechanical Characteristics**Temperature**

UL Rating	Operating
90°C Wet/Dry	-40°C to 90°C

Table Notes: -40C

Bend Radius

Stationary Min.
6.5 in

Max. Pull Tension: 223 lbs

Bulk Cable Weight: 165 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Flammability / Fire Resistance:	UL1581 Vertical Tray, FT4, 60332-3-24 (Category C)
NEC / UL Compliance:	Article 336, TC-ER
AWM Compliance:	AWM I A/B II A/B
CEC / C(UL) Compliance:	CIC, TC
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ISA/SP-50 Type A

History

Update and Revision: Revision Number: 0.407 Revision Date: 05-26-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.