



Product: [2138A](#)

Category 5e Indoor/Outdoor CMR/CMX F/UTP Cable

Product Description

CAT5e (100MHz), 4-Pair, F/UTP-Foil shielded, Riser-CMR-CMX Outdoor, Premise Horizontal Cable, 24 AWG solid bare copper conductors, polyolefin insulation, overall Beldfoil® shield,PVC jacket, RJ-45 compatible

Technical Specifications

Product Overview

Suitable Applications:	OSP-Outdoor, Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 100MHz Category 5e
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	24

Outer Jacket Material

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.265 in	No

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
93.8 Ohm/km	5 %

Capacitance

Max. Capacitance Unbalance	Nom.Mutual Capacitance
330 pF/100m	15 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew
100 MHz	537.6 ns/100m	45 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	65.3 dB	62.3 dB	63.3 dB	60.3 dB	63.8 dB	60.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	52.2 dB	49.2 dB	51.8 dB	48.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46.0 dB	43.0 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43.8 dB	40.8 dB	43.8 dB	40.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
16 MHz	8.2 dB/100m	47.2 dB	44.2 dB	39.0 dB	36.0 dB	39.7 dB	36.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.8 dB	34.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31.2 dB	28.2 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm
62.5 MHz	17.0 dB/100m	38.4 dB	35.4 dB	21.4 dB	18.4 dB	27.9 dB	24.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
100 MHz	22.0 dB/100m	35.3 dB	32.3 dB	13.3 dB	10.3 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm
155 MHz	28.1 dB/100m	32.4 dB	29.4 dB	4.4 dB	1.4 dB	20.0 dB	17.0 dB	18.8 dB		
200 MHz	32.4 dB/100m	30.8 dB	27.8 dB	-1.6 dB	-4.6 dB	17.8 dB	14.8 dB	18.0 dB		

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	-20°C To +75°C
UL Temp Rating:	90°C
Storage Temp Range:	-40°C To +75°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Cold Bend Test:	-40°C Compliance Per UL 1581
Bulk Cable Weight:	31 lbs/1000ft
Max. Pull Tension:	25 lbs
Min Bend Radius During Installation:	2.75 in
Min Bend Radius/Minor Axis:	2.25 in

Standards

NEC/(UL) Compliance:	CMG, CMR, CMX-Outdoor
CEC/C(UL) Compliance:	CMR-CMX OUTDOOR OR CMG
IEC Compliance:	11801 ed 2.2 (2011) Class D
CPR Euroclass:	Yes
Data Category:	Category 5e
ANSI Compliance:	S-90-661-2012 Category 5e, ANSI/NEMA WC-63.1 Category 5e
TIA/EIA Compliance:	ANSI/TIA-568-C.2 Category 5e
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3
Other Compliance:	Outdoor Use ANSI/ICEA S56434, Broadband Outdoor Use ANSI/ICEA S99689, Indoor/Outdoor Use ANSI/ICEA S100685
Third Party Performance Verification:	Category 5e

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes

EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2016-01-19

Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL 1666 Riser
CSA Flammability:	FT4
IEC Flammability:	60332-1
IEEE Flammability:	1202 Vertical Tray
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1533P

Part Number

Non-Plenum Number:	1533R
--------------------	-------

Variants

Item #	Color	UPC
2138A 0101000	Black	612825377320

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 100 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0. Shield is Bonded to Jacket Inner Wall for Electrical Stability.
--------	--

History

Update and Revision:	Revision Number: 0.213 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.