



**Product:** [2146A](#) 

Category 6 Indoor/Outdoor Cable, 4 Pair, U/UTP, CMR/CMX

## Product Description

Category 6 Premise Horizontal Cable (350MHz), Indoor/Outdoor, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Riser-CMR/CMX Outdoor, UV Resistant PVC Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Indoor/Outdoor, Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a> .

### Construction Details

#### Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

#### Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe and Blue, White/Orange Stripe and Orange, White/Green Stripe and Green, White/Brown Stripe and Brown
Bonded-Pair:	No

#### Outer Jacket

Separator Material	Material	Nom. Diameter	Ripcord
Dielectric Tape (Patented)	PVC - Polyvinyl Chloride	0.255 in	Yes

### Electrical Characteristics

#### Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. Capacitance Unbalance	Nom. Mutual Capacitance
78 Ohm/km	3%	330 pF/100m	17 pF/ft

#### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	35 ns/100m	68%

#### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Min. TCL [dB]	Min. ELTCL [dB]
1 MHz	2.0 dB/100m	75.3 dB	75.3 dB	73.3 dB	73.3 dB	70.8 dB	67.8 dB	20.0 dB	100 +/- 15	40.0 dB	35.0 dB
4 MHz	3.7 dB/100m	66.3 dB	66.3 dB	62.5 dB	62.5 dB	58.8 dB	55.8 dB	23.0 dB	100 +/- 15	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	61.8 dB	61.8 dB	56.5 dB	56.5 dB	52.7 dB	49.7 dB	24.5 dB	100 +/- 15	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	60.3 dB	60.3 dB	54.4 dB	54.4 dB	50.8 dB	47.8 dB	25.0 dB	100 +/- 15	40.0 dB	15.0 dB
16 MHz	7.4 dB/100m	57.2 dB	57.2 dB	49.8 dB	49.8 dB	46.7 dB	43.7 dB	25.0 dB	100 +/- 15	38.0 dB	10.9 dB
20 MHz	8.3 dB/100m	55.8 dB	55.8 dB	47.4 dB	47.4 dB	44.8 dB	41.8 dB	25.0 dB	100 +/- 15	37.0 dB	9.0 dB
25 MHz	9.4 dB/100m	54.3 dB	54.3 dB	45.0 dB	45.0 dB	42.8 dB	39.8 dB	24.3 dB	100 +/- 15	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	52.9 dB	52.9 dB	42.4 dB	42.4 dB	40.9 dB	37.9 dB	23.6 dB	100 +/- 15	35.1 dB	5.1 dB

62.5 MHz	15.1 dB/100m	48.4 dB	48.4 dB	33.3 dB	33.3 dB	34.9 dB	31.9 dB	21.5 dB	100 +/- 15	32.0 dB
100 MHz	19.3 dB/100m	45.3 dB	45.3 dB	26.0 dB	26.0 dB	30.8 dB	27.8 dB	20.8 dB	100 +/- 15	30.0 dB
155 MHz	24.5 dB/100m	42.4 dB	42.4 dB	17.9 dB	17.9 dB	27.0 dB	24.0 dB	19.5 dB	100 +/- 22	28.1 dB
200 MHz	28.2 dB/100m	40.8 dB	40.8 dB	12.6 dB	12.6 dB	24.8 dB	21.8 dB	18.7 dB	100 +/- 22	27.0 dB
250 MHz	31.8 dB/100m	39.3 dB	39.3 dB	7.5 dB	7.5 dB	22.8 dB	19.8 dB	18.0 dB	100 +/- 32	26.0 dB
300 MHz	35.2 dB/100m	38.1 dB	36.1 dB	2.9 dB	0.9 dB	21.3 dB	18.3 dB	17.5 dB	100 +/- 32	25.2 dB
350 MHz	38.4 dB/100m	37.1 dB	35.1 dB			19.9 dB	16.9 dB	17.0 dB	100 +/- 32	24.6 dB
400 MHz	41.5 dB/100m	36.3 dB	34.3 dB			18.8 dB	15.8 dB	16.6 dB	100 +/- 32	24.0 dB
450 MHz	44.3 dB/100m	35.5 dB	33.5 dB			17.7 dB	14.7 dB	16.2 dB	100 +/- 32	23.5 dB
500 MHz	47.1 dB/100m	34.8 dB	32.8 dB			16.8 dB	13.8 dB	15.9 dB	100 +/- 32	23.0 dB
550 MHz	49.7 dB/100m	34.2 dB	32.2 dB			16.0 dB	13.0 dB	15.6 dB	100 +/- 32	

#### Voltage

UL Voltage Rating
300 V (CMR), 300 V (CMX-Outdoor)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating	Installation	Storage
90°C	-40°C To +75°C	-20°C To +75°C	-40°C To +75°C

#### Bend Radius

Installation Min.
2.75 in

Max. Pull Tension:	25 lbs
Bulk Cable Weight:	29 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	UL 1666 Riser, FT4, FT4, IEEE 1202 Vertical Tray Flame Test
NEC / UL Compliance:	Article 800, CMR;CMX-Outdoor;CMG
CEC / C(UL) Compliance:	CMX-Outdoor;CMG
ICEA Compliance:	S-116-732-2013, S-56-434, S-99-689, S-100-685
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
GENELEC Compliance:	Segregation class according EN50174-2=a
CPR Euroclass:	Fca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

### Part Number

Plenum Number:	2413
Non-Plenum Number:	2412

#### Variants

Item #	Color	UPC
2146A 0101000	Black	612825062264

### Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

### History

Update and Revision:	Revision Number: 0.275 Revision Date: 10-13-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.