



**Product:** [2221](#)

Audio Cable, 2 Conductor 26 AWG, TC

### Product Description

26 AWG stranded (30x40) BC conductors cabled with fillers, Datalene® insulation, conductors cabled with fillers, TC "French Braid" Shield (95% coverage), Belflex PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
26	30x40	BC - Bare Copper	1

Conductor Count:	2
Total Number of Pairs:	1

##### Insulation

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
PE - Polyethylene (Foam)	Datalene®	0.050 in	0.015 in

##### Color Chart

Number	Color
1	Red & Black

##### Outer Shield

Type	Material	Coverage [%]
French Braid	Tinned Copper (TC)	95%

##### Outer Jacket

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	Belflex®	0.17 in	0.0245 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR
36 Ohm/1000ft	36 Ohm/1000ft		6.6 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Conductor
13 pF/ft

##### Impedance

Nominal Characteristic Impedance
110 Ohm

## Delay

### Nominal Velocity of Propagation (VP) [%]

78%

## Current

### Max. Recommended Current [A]

1.9 Amps per Conductor

## Voltage

### UL Voltage Rating

300 V RMS

## Temperature Range

Operating Temperature Range: -20°C To +60°C

## Mechanical Characteristics

Bulk Cable Weight: 16.5 lbs/1000ft

Max. Pull Tension: 34 lbs

Min. Bend Radius/Minor Axis: 1.75 in

## Standards

Other Specification: AES/EBU Digital Audio

## Applicable Environmental and Other Programs

Environmental Space: Indoor (Not Riser or Plenum)

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/11/EC (BFR): Yes

EU Directive 2011/65/EU (RoHS 2): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU (RoHS 2 amendment): Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

MII Order #39 (China RoHS): Yes

## Suitability

Suitability - Indoor: Yes

## Flammability, LSOH, Toxicity Testing

UL voltage rating: 300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N): No

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
2221 B59U1000	Black, Matte	UnReel	1,000 ft	612825130840
2221 G7XU1000	Blue, Matte	UnReel	1,000 ft	612825130871
2221 G7WU1000	Green, Matte	UnReel	1,000 ft	612825130864
2221 B02U1000	Purple	UnReel	1,000 ft	612825130833
2221 G7VU1000	Red, Matte	UnReel	1,000 ft	612825130857

## Product Notes

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

## History

Update and Revision: Revision Number: 0.403 Revision Date: 02-15-2024

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.