



Product: [22629D](#) 

CIC 300V, 4 Pr #16 Str BC, XLPE Ins E1, IS/OS, Blk PVC Jkt, 90C Dry/Wet
SUN RES -25C

Product Description

Canadian Instrumentation Cable TC-CIC 300V, 4 Pair 16AWG (7x24) Bare Copper, XLPE Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, 90C Dry/Wet SUN RES -25C

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material
Pair(s)	16	7x24	TC - Tinned Copper

Conductor Count: 8

Insulation

Element	Material	Nominal Diameter	Nominal Wall Thickness
Pair(s)	XLP, XLPO, XLPE (Thermoset)	0.108in mm	0.025 in

Color Chart

Color
Black & White and numbered

Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	18	7x26

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.628 in	0.063 in	Yes

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Inner Shield DCR	Nominal Outer Shield DCR
4.6 Ohm/1000ft	4.71 Ohm/1000ft	3.62 Ohm/1000ft

Current

Max. Recommended Current [A]
4.48 Amps per Conductor at 30°C

Voltage

Description	Non-UL Voltage Rating
CEC CIC	300 V

Temperature Range

Installation Temperature Range:	-25°C To +105
Non-UL Temp Rating:	105°C
Operating Temperature Range:	-40°C To +105°C

Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	202 lbs/1000ft
Maximum Recommended Pulling Tension:	343.7 lbs
Minimum Bend Radius During Installation:	7.536 in

Standards

CEC/C(UL) Compliance:	C1C
CSA AWM Compliance:	C22.2#239, Type C1C, C22.2#0.3, Clause 4.31, Low Acid Test

Applicable Environmental and Other Programs

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
--------------------------	-------------------------------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

History

Update and Revision:	Revision Number: 0.244 Revision Date: 10-23-2026
----------------------	--

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.