



**Part Number: 2285P**

Light Dimmer Cable, 2 Conductor 18 AWG BC, CMP

**Product Description**

Light Dimmer Cable, 2 Conductor 18 AWG solid bare copper conductors with Flamarrest® insulation, CMP rating, Flamarrest® Low Smoke PVC jacket with ripcord.

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor - Plenum
Suitable Applications:	Ballast Wiring and Connection, Addressable Fire Systems, Data Circuits, Monitor/Detection, Control Circuits, Initiating Circuits, Notification Circuits

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
18	Solid	BC - Bare Copper	0.0407 in	2

Conductor Count:	2
Conductor Size:	18 AWG

**Insulation**

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.0585 in	0.009 in

**Color Chart**

Number	Color
1	Violet
2	Gray

**Outer Shield Material**

Material
Unshielded

**Outer Jacket Material**

Material	Nominal Diameter	Nominal Wall Thickness
LS PVC - Low Smoke Polyvinyl Chloride	0.147 in	0.015 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
6.4 Ohm/1000ft

**Current**

Max. Recommended Current [A]
per conductor @ 25°C: 5 A

**Voltage**

UL Voltage Rating
-------------------

300 V RMS

## Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	0°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	15.7 lbs/1000ft
Max Recommended Pulling Tension:	39.2 lbs
Min Bend Radius/Minor Axis:	1.5 in

## Standards

NEC Articles:	800
NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262 Plenum Flame Test (UL910)
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Part Number

Non-Plenum Number:	2285R
--------------------	-------

## Variants

Item #	Color
2285P 0091000	White
2285P 0091000	White
2285P 009500	White
2285P 009500	White

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.