



**Product:** [23507D](#)

ACIC 300V, 1 Tri #16 Str TC, XLPE Ins E1, OS, PVC Jkt, AIA Armor, Blk PVC Jkt, 90C Dry/Wet CSA HLBCD SUN RES -40C

### Product Description

Canadian Instrumentation Cable TC-ACIC 300V, 1 Triad 16AWG (7x24) Tinned Copper, XLPE Insulation E1 Color Code, Overall Beldfoil® Shield, PVC Inner Jacket, Aluminum Interlock Armor, Black PVC Outer Jacket, 90C Dry/Wet CSA HLBCD SUN RES -40C

### Technical Specifications

#### Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), encoders, control circuits, distributed control system (DCS), programmable logic controller (PLC), Solenoids, Valves, Actuators, Positioners
------------------------	---

#### Construction Details

##### Conductor

Element	Number of Element	Size	Stranding	Material
Triad(s)	1	16 AWG	7x24	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Triad(s)	XLP, XLPO, XLPE (Thermoset)	0.025 in (0.64 mm)	0.108 in mm	Black, White & Red

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

##### Inner Jacket

Material	Nom. Thickness	Nom. Diameter	Color
PVC - Polyvinyl Chloride	0.047 in (1.2 mm)	0.329 in (8.36 mm)	Black

##### Armor

Armor Type & Material	Armor Thickness	Diameter Over Armor
AIA - Aluminum Interlock Armor	0.509 in (12.9 mm)	0.514 in (13.1 mm)

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.052 in (1.3 mm)	0.613 in (15.6 mm)	Yes

Overall Cable Diameter (Nominal):	0.613 in (15.6 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Max. Current
4.6 Ohm/1000ft	6.4 Amps per Conductor at 30°C

##### Voltage

Voltage Rating
300 V

## Mechanical Characteristics

### Temperature

Operating
-40°C To +105°C Dry/90°C Wet

### Bend Radius

Stationary Min.	Installation Min.
7.356 in (186.8 mm)	7.356 in (186.8 mm)

Max. Pull Tension:	319.7 lbs (145.0 kg)
Bulk Cable Weight:	190 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, UV Resistance
Flammability / Reaction to Fire:	FT4
CEC / C(UL) Compliance:	HLBCD

## History

Update and Revision:	Revision Number: 0.57 Revision Date: 01-23-2023
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.