



**Product:** [23509](#)

ACIC 300V, 4 Pr #16 Str TC, PVC Ins E1, IS/OS, PVC Jkt, AIA Armor, PVC Jkt, 105C Dry 75C Wet CSA HLABCD SUN RES -40C

## Product Description

Canadian Instrumentation Cable TC-ACIC 300V, 4 Pair 16AWG (7x24) Tinned Copper, PVC Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, PVC Inner Jacket, Aluminum Interlock Armor, PVC Outer Jacket, 105C Dry 75C Wet CSA HLABCD SUN RES -40C

## Technical Specifications

### Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), encoders, control circuits, distributed control system (DCS), programmable logic controller (PLC), Solenoids, Valves, Actuators, Positioners
------------------------	---

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	4	16 AWG	7x24	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.108 in (2.74 mm)	Black and White and Numbered

#### Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	16 AWG (7x24) TC

#### Inner Jacket

Material	Nom. Thickness	Nom. Diameter	Color
PVC - Polyvinyl Chloride	0.063 in (1.6 mm)	0.628 in (16.0 mm)	Black

#### Armor

Armor Type & Material	Armor Thickness	Diameter Over Armor
AIA - Aluminum Interlock Armor	0.025 in (0.64 mm)	0.853 in (21.7 mm)

#### Outer Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.957 in	Yes

Overall Cable Diameter (Nominal):	0.957 in
-----------------------------------	----------

### Electrical Characteristics

#### Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR
4.2 Ohm/1000ft	5.4 Ohm/1000ft (18 Ohm/km)

## Voltage

### Voltage Rating

300 V (CEC ACIC)

## Mechanical Characteristics

### Temperature

Operating	Installation
Dry: -40°C to +105°C, Wet: -40°C to +75°C	-25°C To +105°C

### Bend Radius

Stationary Min.	Installation Min.
11.48 in (291.6 mm)	11.48 in

Max. Pull Tension:	200 lbs (91 kg)
Bulk Cable Weight:	387 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
CEC / C(UL) Compliance:	ACIC, HLABCD, ACIC
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.372 Revision Date: 02-03-2025
----------------------	--

## Part Numbers

### Variants

Item #	Putup Type	UPC
23509 06010000	Reel	612825322481
23509 0602500	Reel	612825322511
23509 0605000	Reel	612825322528
23509 0605000	Reel	612825322528
23509 0607500	Reel	612825322535
23509 0085000	Reel	
23509 0602500	Reel	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.