



REPRESENTATIVE IMAGE

Product: [2451RW](#)

Indoor/Outdoor Stadium, Line Level Audio Cable, 1 Pr #22 Str TC, O/A Foil, CPE Jkt, CMR, Waterblocked

Product Description

Line Level Audio Cable, 1 Pair 22 AWG (7x30) Tinned Copper, PP Insulation, Overall Beldfoil® Shield, Waterblocking Tape, CPE jacket, CMR

Technical Specifications

Product Overview

Suitable Applications:	Line level audio; Low voltage analog signals; Dual-purpose indoor/outdoor with no transition, Below-grade, Wet locations
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.009 in (0.23 mm)	0.046 in (1.2 mm)	Black & Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Waterblocking:	Waterblock Tape
----------------	-----------------

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
CPE - Chlorinated Polyethylene	0.023 in (0.58 mm)	0.158 in (4.01 mm)

Overall Cable Diameter (Nominal):	0.158 in (4.01 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.5 Ohm/1000ft (47.6 Ohm/km)	34 pF/ft (110 pF/m)	67 pF/ft (220 pF/m)	45 Ohm	66%	2.9 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V (CMR)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.

1.6 in (41 mm) | 1.6 in (41 mm)

Max. Pull Tension:	27 lbs (12 kg)
Bulk Cable Weight:	13 lbs/1000ft (19 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Water Exposure/Below-Grade Conduit, Indoor, Outdoor, UV Resistance, Aerial - When supported by messenger wire
Flammability / Reaction to Fire:	UL1666 Riser
NEC / UL Compliance:	Article 800, CMR
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Print legend includes sequential footage marks.
--------	---

History

Update and Revision:	Revision Number: 0.167 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
2451RW 0101000	Black	Reel	1,000 ft	612825384847	
2451RW 0105000	Black	Reel	5,000 ft	612825384854	C Z

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.