



Product: [25100UE](#)

Security & Sound, 2 Conductor 14 AWG BC, Armored

Product Description

Security & Commercial Audio Cable, Armored, 2 Conductor 14 AWG stranded (19x27) bare copper conductors with polyolefin insulation, PVC jacket.

Technical Specifications

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	14 AWG	19x26	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.011 in (0.28 mm)	0.092 in (2.3 mm)	Black, White

Outer Shield

Shield Type	Material	Coverage
Tape	Polyester	100%

Inner Jacket

Material	Nom. Thickness	Nom. Diameter	Color
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.230 in (5.84 mm)	Brown

Armor

Armor Type & Material	Armor Thickness	Diameter Over Armor
AIA - Aluminum Interlock Armor	0.025 in (0.64 mm)	0.45 in (11 mm)

Overall Cable Diameter (Nominal): 0.45 in

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
2.53 Ohm/1000ft	22 pF/ft (72 pF/m)	8 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
4.5 in (110 mm)	4.5 in

Max. Pull Tension:	200 lbs (91 kg)
Bulk Cable Weight:	81 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL1666 Riser
NEC / UL Compliance:	Article 725, Article 760
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6100UE

History

Update and Revision:	Revision Number: 0.242 Revision Date: 12-20-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
25100UE 0001000	None	Reel	1,000 ft	612825132059	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.