




**Product:** [27080C](#) 

TC XLPE/PVC, 2 C #14 Str BC, XLPE Ins E2, Blk PVC Jkt, 600V TC 90C Dry/Wet SUN RES DIR BUR

## Product Description

UL Type TC (1277) XLPE/PVC, 2 Conductor 14AWG (7x22) Bare Copper, XLPE Insulation E2 Color Code, Black PVC Outer Jacket, 600V TC 90C Dry/Wet SUN RES DIR BUR

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
14	7x22	BC - Bare Copper	0.071 in	2

Conductor Count:	2
------------------	---

#### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.133 in	0.031 in

#### Color Chart

Color
E2 Colored & Numbered
Red

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.23 x 0.360 in	0.047 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
2.6 Ohm/1000ft

#### Voltage

UL Description	UL Voltage Rating	Voltage Rating [V]
TC	600 V RMS (Type TC)	600 V RMS (Type TC)

### Temperature Range

UL Temp Rating:	90°C Dry, 90°C Wet
Operating Temp Range:	-30°C To +90°C
Wet Temp Range:	-30°C To +90 °C
Dry Temp Range:	-30°C To +90 °C

### Mechanical Characteristics

Bulk Cable Weight:	81 lbs/1000ft
Max. Pull Tension:	108 lbs
Min Bend Radius (Overall):	3.2 in

Min Bend Radius/Minor Axis:	0.92 in
-----------------------------	---------

## Standards

NEC/(UL) Compliance:	TC, XHHW-2
IEEE Compliance:	1202

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2000/53/EC (ELV); EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

## Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Putup Type	UPC
27080C 01010000	Reel	612825325734
27080C 01010000	Reel	612825325734
27080C 0105000	Reel	
27080C 0105000	Reel	

## History

Update and Revision:	Revision Number: 0.87 Revision Date: 02-16-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.