



Product: [22635](#) 

CIC 300V, 8 Pr #18 Str TC, PVC Ins E1, IS/OS, Blk PVC Jkt, 105C Dry 75C Wet SUN RES -25C

Product Description

Canadian Instrumentation Cable TC-CIC 300V, 8 Pair 18AWG (7x26) Tinned Copper, PVC Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, 105C Dry 75C Wet SUN RES -25C

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Pairs
Pair(s)	18	7x26	TC - Tinned Copper	8

Conductor Count:	16
------------------	----

Insulation

Material
PVC - Polyvinyl Chloride

Color Chart

Color
Black & White numbered

Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	22	7x30

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord	Separator Material
PVC - Polyvinyl Chloride	0.73 in	0.06 in	Yes	Polyester Tape

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
10.3 Ohm/1000ft	6.7 Ohm/1000ft	4.8 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
42 pF/ft	95 pF/ft

Inductance

Nominal Inductance
0.19 µH/ft

Current

Max. Recommended Current [A]

3.5 Amps per Conductor at 25°C

Voltage

Non-UL Description	Non-UL Voltage Rating
CEC CIC	300 V

Temperature Range

Installation Temperature Range:	-25°C To +105
Non-UL Temp Rating:	105°C
Operating Temperature Range:	-40°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	570 lbs/1000ft
Minimum Minor Axis Bend Radius:	7.3 in

Standards

CEC/C(UL) Compliance:	CIC
CSA AWM Compliance:	C22.2#239, Type CIC, C22.2#0.3, Clause 4.31, Low Acid Test

Applicable Environmental and Other Programs

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Flammability, LS0H, Toxicity Testing

CSA/C(UL) Flammability:	FT4
-------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

History

Update and Revision:	Revision Number: 0.416 Revision Date: 06-10-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.