



Product: [2424](#) 

Category 6+ Enhanced Cable, 4 Pair, U/UTP, LSZH

Product Description

Category 6+ Enhanced Premise Horizontal Cable (350MHz), 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Haloarrest® LSZH Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
------------------------	---

Construction Details

Conductor

Size	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Outer Jacket

Separator	Material	Material Trade Name	Nom. Diameter	Ripcord
Dielectric Tape (Patented)	LSZH - Low Smoke Zero Halogen (Flame Retardant)	Haloarrest®	0.221 in (5.61 mm)	Yes

Overall Cable Diameter (Nominal):	0.221 in (5.61 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
78 Ohm/km	160 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	35 ns/100m	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1	2.0 dB/100m	79.3	77.3	77.3	75.3	70.8	67.8	20.0	100 ± 15	102 ± 15
4	3.7 dB/100m	70.3	68.3	66.5	64.5	58.8	55.8	23.6	100 ± 15	100 ± 15
8	5.3 dB/100m	65.8	63.8	60.5	58.5	52.7	49.7	25.3	100 ± 15	100 ± 15
10	5.9 dB/100m	64.3	62.3	58.4	56.4	50.8	47.8	26.0	100 ± 15	100 ± 15
16	7.4 dB/100m	61.2	59.2	53.8	51.8	46.7	43.7	26.0	100 ± 15	100 ± 15
20	8.3 dB/100m	59.8	57.8	51.4	49.4	44.8	41.8	26.0	100 ± 15	100 ± 15
25	9.4 dB/100m	58.3	56.3	49.0	47.0	42.8	39.8	25.5	100 ± 15	100 ± 15
31.25	10.5 dB/100m	56.9	54.9	46.4	44.4	40.9	37.9	25.0	100 ± 15	100 ± 15
62.5	15.1 dB/100m	52.4	50.4	37.3	35.3	34.9	31.9	23.5	100 ± 15	100 ± 15
100	19.3 dB/100m	49.3	47.3	30.0	28.0	30.8	27.8	22.5	100 ± 15	100 ± 15
155	24.5 dB/100m	46.4	44.4	21.9	19.9	27.0	24.0	21.6	100 ± 22	100 ± 15

200	28.2 dB/100m	44.8	42.8	16.6	14.6	24.8	21.8	21.0	100 ± 22	100 ± 15
250	31.8 dB/100m	43.3	41.3	11.5	9.5	22.8	19.8	20.5	100 ± 32	100 ± 15
300	35.2 dB/100m	42.1	40.1	6.9	4.9	21.3	18.3	20.1	100 ± 32	100 ± 15
350	38.4 dB/100m	41.1	39.1	2.7	0.7	19.9	16.9	19.8	100 ± 32	100 ± 15
400	41.5 dB/100m	40.3	38.3			18.8	15.8	19.5	100 ± 32	100 ± 15
450	44.3 dB/100m	39.5	37.5			17.7	14.7	19.2	100 ± 32	100 ± 15
500	47.1 dB/100m	38.8	36.8			16.8	13.8	19.0	100 ± 32	100 ± 15
550	49.7 dB/100m	38.2	36.2			16.0	13.0	18.8	100 ± 32	100 ± 15

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-20°C To +75°C	+5°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.0 in (25 mm)	2.25 in

Max. Pull Tension:	25 lbs (11 kg)
Bulk Cable Weight:	23 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Eca, Indoor, Non-Halogenated
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	N/A
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
Third Party Performance Verification:	Category 6
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CENELEC Compliance:	Segregation class according EN50174-2 = a
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2017-07-10
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	2413

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.463 Revision Date: 05-04-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN
2424.06305	Blue	Reel	305 m	8719605005038
2424.0061000	Blue	Reel	1,000 ft	612825061557
2424.08305	Gray	Reel	305 m	8719605005069
2424.07305	Purple	Reel	305 m	8719605005052
2424.0071000	Purple	Reel	1,000 ft	612825061540
2424.071000	Purple	Reel	1,000 m	8719605005045
2424.02500	Red	Reel	500 m	8719605005021
2424.0091000	White	Reel	1,000 ft	612825061564

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.