



**Product:** [27110QU](#)

TC XLPE/CPE, 3+G C #12+12 Str BC, XLPE Ins E2, Blk CPE Jkt, 600V TC 90C Dry/Wet SUN RES

## Product Description

UL Type TC (1277) XLPE/CPE, 3+G Conductor 12+12AWG (7x20) Bare Copper, XLPE Insulation E2 Color Code, Black CPE Outer Jacket, 600V TC 90C Dry/Wet SUN RES

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors
12	7x20	BC - Bare Copper	3
12		BC - Bare Copper	1

Conductor Count: 3

#### Insulation

Material	Nominal Diameter
XLP, XLPO, XLPE (Thermoset)	0.150 in
No Insulation	

#### Color Chart

Number	Color
1	Black
2	Red
3	Blue

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
CPE - Chlorinated Polyethylene	0.437 in	0.047 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
1.65 Ohm/1000ft

#### Current

Max. Recommended Current [A]
30 Amps per Conductor at 30°C

#### Voltage

Description	UL Description	UL Voltage Rating	Voltage Rating [V]
Type TC	TC	600 V RMS (Type TC)	600 V RMS (Type TC)

### Temperature Range

UL Temp Rating:	90°C Dry, 90°C Wet
Operating Temp Range:	-30°C To +90°C

Wet Temp Range:	-30°C To +90 °C
Dry Temp Range:	-30°C To +90 °C

## Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	140 lbs/1000ft
Max. Pull Tension:	154 lbs
Min Bend Radius/Minor Axis:	1.75 in

## Standards

NEC/(UL) Compliance:	TC, XHHW-2
Other Compliance:	ICEA S-73-532, S-95-658, S-61-524

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01

## Suitability

Suitability - Burial:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL 1685 UL Loading
CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Putup Type
27110QU 0107500	Reel

## History

Update and Revision:	Revision Number: 0.30 Revision Date: 06-24-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.