




Product: [27292](#) 

MC XLPE/PVC, 37+G C #14+14 Str BC, XLPE Ins E2, AIA Armor, Blk PVC Jkt, 600V MC 90C Dry/Wet SUN RES DIR BUR CT USE

Product Description

UL Type MC (1569) XLPE/PVC, 37+G Conductor 14+14AWG (7x22) Bare Copper, XLPE Insulation E2 Color Code, Aluminum Interlock Armor, Black PVC Outer Jacket, 600V MC 90C Dry/Wet SUN RES DIR BUR CT USE

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
14	7x22	BC - Bare Copper	37
14		BC - Bare Copper	1

Conductor Count:	37
------------------	----

Insulation

Material	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.03 in
No Insulation	

Color Chart

Number	Color
1	Black
2	Red
3	Blue
4	Orange
5	Yellow
6	Brown
7	Red/Black
8	Blue/Black
9	Orange/Black
10	Yellow/Black
11	Brown/Black
12	Black/Red
13	Blue/Red
14	Orange/Red
15	Yellow/Red
16	Brown/Red
17	Black/Blue
18	Red/Blue
19	Orange/Blue
20	Yellow/Blue
21	Brown/Blue
22	Black/Orange
23	Red/Orange
24	Blue/Orange
25	Yellow/Orange

26	Brown/Orange
27	Black/Yellow
28	Red/Yellow
29	Blue/Yellow
30	Orange/Yellow
31	Brown/Yellow
32	Black/Brown
33	Red/Brown
34	Blue/Brown
35	Orange/Brown
36	Yellow/Brown
37	Black

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	1.303 in	0.055 in

Construction and Dimensions

Armor

Type of Armor	Material	Diameter over Armoring
Interlocked	Aluminum	1.193 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
2.6 Ohm/1000ft

Current

Max. Recommended Current [A]
6 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
600 V RMS

Temperature Range

UL Temp Rating:	90°C Dry, 90°C Wet
Operating Temp Range:	-40°C To +90°C
Wet Temp Range:	-40°C To +90 °C
Dry Temp Range:	-40°C To +90 °C

Mechanical Characteristics

Bulk Cable Weight:	1031 lbs/1000ft
Max. Pull Tension:	1190 lbs
Min Bend Radius/Minor Axis:	16.1 in

Standards

NEC/(UL) Compliance:	MC, XHHW-2, UL1569
----------------------	--------------------

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-13
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Putup Type	UPC
27292 0105000	Reel	612825328766
27292 0105000	Reel	612825328766

History

Update and Revision:	Revision Number: 0.185 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.