



Product: [28081C](#) 

TC XLPE/PVC, 3 C #14 Str BC, XLPE Ins E2, Blk PVC Jkt, 600/1000V TC-ER 90C Dry/Wet SUN RES DIR BUR

Product Description

UL Type TC (1277) XLPE/PVC, 3 Conductor 14AWG (7x22) Bare Copper, XLPE Insulation E2 Color Code, Black PVC Outer Jacket, 600V TC-ER 90C Dry/Wet SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications:	Power and Control Applications up to 600/1000V Class 1 Division 2 Hazardous Locations; Recommended Cable Gland Belden BTC075A0551RA
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	14	7x22	BC - Bare Copper	3

Conductor Count:	3
------------------	---

Insulation

Element	Material	Nominal Diameter	Nominal Wall Thickness
Conductor(s)	XLP, XLPO, XLPE (Thermoset)	0.132 in	0.031 in

Color Chart

Number	Color
ICEA S-73-732 Table E2 (colored and numbered)	Black
	Red
	Blue

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.378 in	0.047 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
2.67 Ohm/1000ft

Current

Max. Recommended Current [A]
25 Amps per Conductor at 30°C

Voltage

UL Description	UL Voltage Rating	Voltage Rating [V]
TC-ER, XHHW-2	600/1000 V	600 V RMS (Type TC)

Temperature Range

UL Temperature Rating:	Wet/Dry : 90°C
Operating Temperature Range:	Wet/Dry: -30°C to 90°C

Wet Temp Range:	-30°C To +90 °C
-----------------	-----------------

Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	88 lbs/1000ft
Maximum Recommended Pulling Tension:	163.8 lbs
Minimum Bend Radius During Installation:	1.89 in
Minimum Minor Axis Bend Radius:	1.52 in

Standards

NEC Articles:	Article 336, Article 310
NEC/(UL) Compliance:	TC-ER, XHHW-2

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor, Direct Burial
----------------------	-------------------------------

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

CSA/C(UL) Flammability:	FT4
UL Flammability:	UL 1685 UL Loading
IEEE Flammability:	IEEE 1202
UL voltage rating:	600 V RMS (Type TC)

History

Update and Revision:	Revision Number: 0.57 Revision Date: 10-06-2026
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.