



**Product:** [29005](#)

600V ACIC, (6) 16 AWG (7x24) BC+Grd, XLPE/PVC/PVC, AIA Armor

**Product Description**

Six 16 AWG stranded (7x24) bare copper conductors plus bare copper ground wire, cross-linked polyethylene insulation, PVC inner jacket, aluminum interlocked armor, PVC outer jacket.

**Technical Specifications**

**Product Overview**

Suitable Applications:	Power and Control Applications up to 600V
------------------------	---

**Construction Details**

**Conductor**

Element	Number of Element	Size	Stranding	Material
Conductor(s)	6	16 AWG	7x24	BC - Bare Copper
Ground Wire	1	16 AWG	7x24	BC - Bare Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLP, XLPO, XLPE (Thermoset)	0.030 in (0.76 mm)	0.118 in (3.00 mm)	White and Numbered, Black and Numbered
Ground Wire	XLP, XLPO, XLPE (Thermoset)	0.030 in (0.76 mm)	0.118 in (3.00 mm)	Green

**Outer Shield**

<b>Material</b>
No Shield

**Inner Jacket**

Material	Nom. Thickness	Nom. Diameter	Ripcord	Color
PVC - Polyvinyl Chloride	0.047 in (1.2 mm)	0.452 in (11.5 mm)	Yes	Black

Table Notes:	Separator-CORR. MYLAR Tape
--------------	----------------------------

**Armor**

Armor Type & Material	Armor Thickness	Diameter Over Armor
AIA - Aluminum Interlock Armor	0.025 in (0.64 mm)	0.677 in (17.2 mm)

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.052 in (1.3 mm)	0.781 in

Overall Cable Diameter (Nominal):	0.781 in
-----------------------------------	----------

**Electrical Characteristics**

**Electricals**

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	4.45 Ohm/1000ft	14.4 Amps per Conductor at 30°C
Ground Wire	4.45 Ohm/1000ft (14.6 Ohm/km)	19 Amps per Conductor at 25°C

**Voltage**

Voltage Rating
600 V

## Mechanical Characteristics

### Temperature

Operating
-40°C To +90°C

### Bend Radius

Stationary Min.	Installation Min.
9.37 in (238 mm)	9.37 in

Max. Pull Tension:	115 lbs (52.2 kg)
Bulk Cable Weight:	271 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	FT4
CEC / C(UL) Compliance:	HL, ACIC
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.234 Revision Date: 07-15-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.