



**Product:** [29503T](#)

VFD 300% Gnd, 3C+G #10 Str TC, XLPE Ins+PVC Grd, OS+TC Brd w/#10 TC Drain, Blk LSZH Jkt, 600/1000V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable WTTC

## Product Description

Belden 300% Ground Flexible VFD, 3 Conductor 10AWG (105x30) Tinned Copper, XLPE Insulation M4 Color Code+PVC Insulated Ground, Overall Beldfoil®+Tinned Copper Braid(85%) Shield w/10AWG Tinned Copper Drain, Black LSZH Outer Jacket, 600/1000V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable WTTC SUN RES DIR BUR

## Technical Specifications

### Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems; Human safety applications with flame or toxicity concerns (low smoke, zero halogen)
------------------------	--

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	3	10 AWG	105x30	TC - Tinned Copper
Ground	1	10 AWG	105x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.046 in (1.2 mm)	Black and Numbered
Ground	PVC - Polyvinyl Chloride	0.046 in (1.2 mm)	Green/Yellow Stripe

#### Outer Shield

Shield Type	Material	Coverage
Tape	Tri-Laminate (Alum+Poly+Alum)	100%
Braid	Tinned Copper (TC)	85%

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.073 in (1.9 mm)	0.690 in (17.5 mm)	Yes

Overall Cable Diameter (Nominal):	0.690 in (17.5 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.969 Ohm/1000ft (3.18 Ohm/km)	26 pF/ft (85 pF/m)	47 pF/ft (150 pF/m)	71 Ohm	55%	40 Amps per Conductor at 30°C (per NEC)

#### Voltage

UL Voltage Rating
1000 V (TC, WTTC, UL Flexible Motor Supply Cable)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating

90°C Dry, 90°C Wet -25°C To +90°C

#### Bend Radius

Stationary Min.	Installation Min.
8.3 in (210 mm)	8.3 in (210 mm)

Max. Pull Tension:	666 lbs (302 kg)
Bulk Cable Weight:	354 lbs/1000ft (527 kg/km)

#### Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 FT4 Loading
NEC / UL Compliance:	Article 336, TC-ER, WTTC, RHW-2, UL Flexible Motor Supply Cable
ICEA Compliance:	S-95-658
APAC Compliance:	China RoHS II (GB/T 26572-2011)

#### History

Update and Revision:	Revision Number: 0.249 Revision Date: 05-04-2022
----------------------	--

#### Part Numbers

##### Variants

Item #	Color	Putup Type	UPC
29503T 0101000	Black	Reel	612825136989
29503T 0105000	Black	Reel	612825136996

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.