



Product: [28156AX](#)

TC VN/PVC, 3 C #4 Str BC, PVC-NYL Ins M4, Blk PVC Jkt, 600V TC-ER 90C Dry/Wet SUN RES DIR BUR

### Product Description

UL Type TC (1277) PVC-Nylon/PVC, 3 Conductor 4AWG (Class B) Bare Copper, PVC-NYL Insulation M4 Color Code, Black PVC Outer Jacket, 600V TC-ER 90C Dry/Wet SUN RES DIR BUR

### Technical Specifications

#### Product Overview

Suitable Applications:	Power and Control Applications up to 600V
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	4 AWG	7x12	BC - Bare Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.049 in (1.2 mm)	0.323 in mm	Black and Numbered

##### Outer Shield

Material
No Shield

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.063 in (1.6 mm)	0.822 in	Yes

Overall Cable Diameter (Nominal): 0.822 in

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Max. Current
0.26 Ohm/1000ft	95 Amps per Conductor at 30°C

##### Voltage

UL Voltage Rating
600 V

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	Wet/Dry: -30°C To +90°C

##### Bend Radius

Stationary Min.	Installation Min.
3.288 in (83.52 mm)	4.11 in

Max. Pull Tension:	1659 lbs (752.5 kg)
Bulk Cable Weight:	547 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, UV Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEEE 1202 FT4
NEC / UL Compliance:	Article 336, TC-ER, THWN-2
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.54 Revision Date: 02-03-2025
----------------------	---

## Part Numbers

### Variants

Item #	Putup Type
28156AX 0105000	Reel

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.