



Product: [29513](#)

VFD 300% Gnd, 3C+G #10 Str TC, XLPE Ins+PVC Gnd, OS+TC Brd, 1 Pr #16 Str TC XLPE IS, Blk PVC Jkt, 600V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable

[Request Sample](#)

Product Description

Belden 300% Ground Flexible VFD, 3 Conductor 10AWG (105x30) Tinned Copper, XLPE Insulation M4 Color Code+PVC Insulated Ground, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, 1 Pair 16AWG (26x30) Tinned Copper XLPE Beldfoil, Black PVC Outer Jacket, 600V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable 1000V CSA AWM I/II A/B 600V CIC TC SUN RES DIR BUR Oil Resistant

Technical Specifications

Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems; Class 1 Division 2 Hazardous Locations
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material	Notes
Conductor(s)	3	10 AWG	105x30	TC - Tinned Copper	
Pair(s)	1	16 AWG	26x30	TC - Tinned Copper	Used as control or brake pair
Ground Wire	1	10 AWG	105x30	TC - Tinned Copper	

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLPE - Cross Linked Polyethylene	0.046 in (1.2 mm)	0.212 in (5.38 mm)	ICEA Chart M4
Pair(s)	XLPE - Cross Linked Polyethylene	0.032 in (0.81 mm)	0.123 in (3.12 mm)	Black, White
Ground	PVC - Polyvinyl Chloride	0.046 in (1.2 mm)	0.212 in (5.38 mm)	Green/Yellow Stripe

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (19x30) TC	Foil-In, Shorting fold

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Tri-Laminate (Alum+Poly+Alum)	100%	10 AWG (105x30) TC
Braid	Tinned Copper (TC)	85%	

Table Notes:	Foil+braid shield on power conductors & Ground only; extra pair has own foil shield.
--------------	--

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.105 in (2.67 mm)	0.985 in (25.0 mm)	Yes

Overall Cable Diameter (Nominal):	0.985 in (25.0 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.969 Ohm/1000ft		46 pF/ft (150 pF/m)	53 pF/ft (170 pF/m)	83 pF/ft (270 pF/m)	37 Ohm	55%	24 Amps per Conductor at 30°C

Pair(s)	4.0 Ohm/1000ft (13 Ohm/km)	4.99 Ohm/1000ft (16.4 Ohm/km)	34 pF/ft (110 pF/m)				40 Amps per Conductor at 30°C (per NEC)
Ground	1.080 Ohm/1000ft (3.543 Ohm/km)						40 Amps per Conductor at 30°C (per NEC)

Voltage

UL Voltage Rating	Voltage Rating
1000 V (UL Flexible Motor Supply Cable), 600 V (TC, C(UL) TC)	1000 V (AWM I/II A/B)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	-40°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
11.8 in (300 mm)	11.8 in (300 mm)

Max. Pull Tension:	857 lbs (389 kg)
Bulk Cable Weight:	493 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 UL Loading, FT4, IEEE 1202 FT4
NEC / UL Compliance:	Article 336, Article 310, TC-ER, RHW-2, UL Flexible Motor Supply Cable
AWM Compliance:	AWM I/II A/B
CEC / C(UL) Compliance:	CIC, TC
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-07-KA070003-MSHA

History

Update and Revision:	Revision Number: 0.634 Revision Date: 06-19-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
29513 010100	Black	Reel	100 ft	612825137580	C
29513 0101000	Black	Reel	1,000 ft	612825137597	C
29513 0103000	Black	Reel	3,000 ft	612825137603	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.