



Product: [29541](#)

VFD 300% Gnd, 3C+G #4 Str TC, XLPE Ins+PVC Gnd, OS+TC Brd w/-3#10 TC Drains, Blk PVC Jkt, 2000V TC-ER 90C Dry/Wet 2000V Flexible Motor Supply Cable WTTC

[Request Sample](#)

Product Description

Belden 300% Ground Flexible VFD, 3 Conductor 4AWG (7x19x25) Tinned Copper, XLPE Insulation M4 Color Code+PVC Insulated Ground, Overall Beldfoil®+Tinned Copper Braid(85%) Shield w/3-10AWG Tinned Copper Drains, Black PVC Outer Jacket, 2000V TC-ER 90C Dry/Wet 2000V Flexible Motor Supply Cable WTTC 1000V CSA AWM I/II A/B 600V CIC TC SUN RES DIR BUR Oil Resistant

Technical Specifications

Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems; High voltage requirements
------------------------	--

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Conductor(s)	3	4	7x19x25	TC - Tinned Copper
Ground	1	4	7x19x25	TC - Tinned Copper

Insulation

Element	Material	Thickness	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.071 in	Black and Numbered
Ground	XLPE - Cross-Linked Polyethylene (Thermoset)	0.071 in	Green/Yellow Stripe

Outer Shield Material

Shield Type	Material	Coverage
Tape + Braid	Tri-Laminate (Alum+Poly+Alum) + Tinned Copper (TC)	100% + 85%

Outer Jacket Material

Material	Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.095 in	1.205 in	Yes

Cable Diameter (Nominal):	1.205 in
---------------------------	----------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.239 Ohm/1000ft	21 pF/ft	38 pF/ft	90 Ohm	55%	95 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
2000 V (TC, C(UL) TC), 1000 V (WTTC, UL Flexible Motor Supply Cable, CSA AWM I/II A/B)

Mechanical Characteristics

Temperature

UL Rating	Operating

90°C Dry, 90°C Wet -40°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
12.05 in	14.5 in

Max. Pull Tension:	2156 lbs
Bulk Cable Weight:	1133 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1685 UL Loading, FT4, FT4, 1202, 383 Vertical Tray Flame Test (70,000 BTU)
NEC / UL Compliance:	Article 336, TC-ER, WTTC, RHW-2, UL Flexible Motor Supply Cable
AWM Compliance:	I/II A/B
CEC / C(UL) Compliance:	CIC, TC
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-07-KA070003-MSHA

History

Update and Revision:	Revision Number: 0.372 Revision Date: 02-24-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.