



Product: [29017](#)

ACIC 600V, 2+G C #16 Str BC, XLPE Ins, PVC Jkt, AIA Armor, Blu PVC Jkt, 90C Dry/Wet CSA HL SUN RES -40C

Product Description

Canadian Instrumentation Cable TC-ACIC 600V, 2+G Conductor 16AWG (7x24) Bare Copper, XLPE Insulation, PVC Inner Jacket, Aluminum Interlock Armor, Blue PVC Outer Jacket, 90C Dry/Wet CSA HL SUN RES -40C

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
16	7x24	BC - Bare Copper	2
16		BC - Bare Copper	1

Conductor Count:	2
------------------	---

Insulation

Material
XLP, XLPO, XLPE (Thermoset)
XLP, XLPO, XLPE (Thermoset)

Color Chart

Number	Color
1	White and Numbered 1
2	Black and Numbered 2

Inner Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.34 in

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.650 in

Construction and Dimensions

Armor

Type of Armor	Material	Diameter over Armoring
Interlocked	Aluminum	0.54 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
4.2 Ohm/1000ft

Current

Max. Recommended Current [A]
10 Amps per Conductor at 25°C

Voltage

Non-UL Voltage Rating
600 V RMS

Temperature Range

Non-UL Temp Rating:	90°C
UL Temp Rating:	N/A
Operating Temp Range:	-40°C To +90°C
Wet Temp Range:	-40°C To +90 °C
Dry Temp Range:	-40°C To +90 °C

Mechanical Characteristics

Bulk Cable Weight:	202 lbs/1000ft
Max. Pull Tension:	62 lbs
Min Bend Radius/Minor Axis:	7.7 in

Standards

CSA AWM Compliance:	C22.2#239, HAZ LOC, C22.2#0.3 Clause 4.31 Low Acid Gas
---------------------	--

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Hazardous Locations:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT4
UL voltage rating:	N/A

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Putup Type	UPC
29017 J2210000	Reel	612825331469
29017 J225000	Reel	612825331476

History

Update and Revision:	Revision Number: 0.187 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.