



Part Number: 3079E

Profibus, 1 Pr #22 Str BC, PO Ins, OS+TC Brd, PVC Jkt, PLTC Profibus DP

[Request Sample](#)

Product Description

Profibus, 1 Pair 22AWG (7x30) Bare Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(65%) Shield, PVC Outer Jacket, PLTC CMG SUN RES Profibus DP

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	BC - Bare Copper	1

Conductor Count:	2
Total Number of Pairs:	1

Insulation

Material
FRFPE - Flame Retardant Foam Polyethylene

Color Chart

Number	Color
1	Red & Green

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum/Polyester	Beldfoil®	100 %
Braid	2	TC - Tinned Copper		65 %

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.315 in

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
3.9 Ohm/1000ft	16 Ohm/1000ft

Capacitance

Nom.Mutual Capacitance
8.5 pF/ft

Inductance

Nominal Inductance
0.267 µH/ft

Impedance

Nominal Characteristic Impedance
150 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
78 %

High Freq

Max. Insertion Loss (Attenuation)	Max./Min. Fitted Impedance
0.51 dB/100m	150 Ohm
1.57 dB/100m	
4.8 dB/100m	

Current

Element	Max. Recommended Current [A]
Per Conductor	2.3 Amps

Voltage

UL Description	UL Voltage Rating
CMG	300 V RMS

Electrical Characteristics Notes:	Capacitance Unbalance @ 1 kHz: Less than 1000 pF/km
-----------------------------------	---

Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-30°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	39 lbs/1000ft
Max Recommended Pulling Tension:	50 lbs
Min Bend Radius/Minor Axis:	3.2 in

Standards

NEC/(UL) Specification:	PLTC
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 20201 (600 V 75°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
3079E B021000	Purple	612825140412	1,000 ft	C
3079E B025000	Purple	612825140443	5,000 ft	C Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

History

Update and Revision:	Revision Number: 0.301 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.