



Product: [3106ENH](#)

RS-485, 1.5Pr #22 Str TC, PO ins, F/B, LSNH Jkt,Eca

Product Description

RS-485, 1.5 Pair AWG 22 Tinned Copper - Stranded, Polyolefin (PO, PE, PP) insulation, Foil + Braid(s) shielding, LSZH / FRNC jacket ,Eca

Technical Specifications

Product Overview

Suitable Applications:	Instrumentation and computer cable. For EIA RS-485 transmissions applications
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper
Conductor(s)	1	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene (Foam)	0.82 mm (0.032 in)	2.40 mm (0.0945 in)	White & Orange, Orange & White, Blue & White
Conductor(s)	PE - Polyethylene		1.57 mm (0.0618 in)	

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC
Braid	Tinned Copper (TC)	65%	

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	1.0 mm (0.039 in)	7.6 mm (0.30 in)

Overall Cable Diameter (Nominal):	7.60 mm (0.299 in)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	48.2 Ohm/km (14.7 Ohm/1000ft)	36.1 pF/m (11.0 pF/ft)	68.6 pF/m	120 Ohm	78%	2.7 Amps per Conductor
Conductor(s)						2.7 Amps per Conductor

Nom. Outer Shield DCR:	9.2 Ohm/km (2.8 Ohm/1000ft)
------------------------	-----------------------------

High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)
Pair(s)	1	1.68 dB/100m

Voltage

Voltage Rating

300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-45°C To +80°C	-15°C To +80°C	-45°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
38 mm (1.5 in)	76 mm (3.0 in)

Max. Pull Tension:	290 N (65 lbf)
Bulk Cable Weight:	64 kg/km (43 lbs/1000ft)

Standards and Compliance

Environmental Suitability:	Indoor, Indoor, Non-Halogenated, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
CENELEC Compliance:	EN 50290-2-20
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark
Other Standard Compliance(s):	DMX-512

History

Update and Revision:	Revision Number: 0.368 Revision Date: 04-08-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
3106ENH.01500				
3106ENH.00305	Black	Reel	305 m	8719605005922

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.