



**Product:** [29525C](#)

VFD, 3C #6 Str BC XLPE Ins + #6 Symm. Seg. Gnd (3 of #12) Str BC, CTS, Bk PVC Jkt, 600/1000V TC-ER 90C Dry/Wet 1000V CSA AWM I/II A/B

[Request Sample](#)

### Product Description

Belden Basics VFD, 3 Conductor 6AWG (7x14) Bare Copper XLPE Insulation M4 Color Code + 6AWG Symmetrical Segmented Ground (3 of 12AWG) Bare Copper Stranded, Overall Dual Copper Tapes Helically Applied Shield, Black PVC Outer Jacket, 600/1000V TC-ER 90C Dry/Wet 1000V CSA AWM I/II A/B SUN RES DIR BUR Oil Resistant

### Technical Specifications

#### Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems; Class 1 Division 2 Locations
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material	Notes
Conductor(s)	3	6 AWG	7x14	BC - Bare Copper	ASTM B3 Copper B8 Class B Stranding
Segmented Ground Wire	3	12 AWG	7x20	BC - Bare Copper	Segmented Grounds (3 Totaling 6AWG)

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLPO - Crosslink Polyolefin	0.047 in (1.2 mm)	0.272 in (6.91 mm)	ICEA Chart M4
Ground Wire	No Insulation			

##### Outer Shield

Shield Type	Material	Coverage
Helical Tape	Bare Copper (BC)	100%
Helical Tape	Bare Copper (BC)	100%

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.063 in (1.6 mm)	0.724 in (18.4 mm)	Yes

Overall Cable Diameter (Nominal):	0.724 in (18.4 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.355 Ohm/1000ft	32 pF/ft (100 pF/m)	63 pF/ft (210 pF/m)	37 Ohm	55%	75 Amps per Conductor at 30°C
	0.056 Ohm/1000ft (0.18 Ohm/km)					30 Amps per Conductor at 30°C

##### Voltage

UL Voltage Rating
1000 V (TC-ER)

#### Mechanical Characteristics

## Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	-40°C To +90°C

## Bend Radius

Stationary Min.	Installation Min.
8.7 in (220 mm)	8.7 in (220 mm)

Max. Pull Tension:	1304.1 lbs (591.53 kg)
Bulk Cable Weight:	461 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEEE 1202 FT4, FT4
NEC / UL Compliance:	Article 336, TC-ER, XHHW-2
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-07-KA070003-MSHA

## History

Update and Revision:	Revision Number: 0.648 Revision Date: 06-19-2024
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
29525C 0101000	Black	Reel	1,000 ft	612825137733
29525C 0105000	Black	Reel	5,000 ft	612825137771

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.