



Part Number: 29528F

VFD 100% Gnd, 3C+3G(Segmented) #1+3 of #6 Str TC+BC, XLPO Ins M4, CTS, Blk TPE Jkt, 600V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable 1000V WTTC

 [Request Sample](#)

Product Description

Belden 100% Ground Flexible VFD, 3 Conductor+3G(Segmented), 1AWG+3 of 6AWG GND (835(19x44)x30) Tinned Copper + Bare Copper, XLPO Insulation M4 Color Code, Overall Dual Copper Tapes Helically Applied Shield, Black TPE Outer Jacket, 600V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable 1000V WTTC 600V CIC TC SUN RES OIL RES II

Technical Specifications

Product Overview

Suitable Applications:	AC Motor drives, VFD, Variable Frequency drives
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
	1	19x44x30	TC - Tinned Copper	3
Ground Wire	6	7x37x30	TC - Tinned Copper	3

Conductor Count:	3
Conductor Size:	1 AWG

Insulation

Material	Nominal Wall Thickness
XLPE - Cross Linked Polyethylene	0.057 in

Color Chart

Number	Color
1	Black and Numbered 1
2	Black and Numbered 2
3	Black and Numbered 3

Outer Shield Material

Type	Layer	Material	Coverage [%]
Tape	1	Spiral Copper	100 %
Tape	2	Spiral Copper	100 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
TPE - Thermoplastic Elastomer	1.243 in	0.083 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
.13 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield

44 pF/ft	79 pF/ft
----------	----------

Inductance

Nominal Inductance
0.146 μ H/ft

Current

Max. Recommended Current [A]
150 Amps per conductor @ 30°C (per NEC)

Voltage

UL Voltage Rating
1000 V RMS (Flexible Motor Supply Cable)
600 V RMS (NEC Type TC)

Temperature Range

UL Temp Rating:	90°C Wet/Dry
Operating Temp Range:	-40C To +90C Wet/Dry

Mechanical Characteristics

Oil Resistance:	Yes - Oil Res II
Bulk Cable Weight:	1439 lbs/1000ft
Max Recommended Pulling Tension:	2650 lbs
Min Bend Radius/Minor Axis:	6.2 in

Standards

NEC Articles:	336 - ER
NEC/(UL) Specification:	TC-ER, WTTC, XHHW-2
CEC/C(UL) Specification:	600V Type CIC TC
Other Specification:	1000V UL Flexible Motor Supply

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-13
CA Prop 65 (CJ for Wire & Cable):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT4
IEEE Flammability:	1202, 383 Vertical Tray Flame Test (70,000 BTU)
UL voltage rating:	1000 V RMS (Flexible Motor Supply Cable)

Part Number

Variants

Item #	Color	UPC	Length
29528F 0103000	Black	612825373384	3,000 ft

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.