



**Product:** [29531F](#)

VFD 100% Gnd, 3C #3/0 Str TC XLPE Ins + #3/0 Symm. Seg. Gnd (3 of #4+) Str TC, CTS, Blk TPE Jkt, 600/1000V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable WTTC

[Request Sample](#)

## Product Description

Belden 100% Ground Extra Flexible VFD, 3 Conductor 3/0AWG (7x7x31x30) Tinned Copper XLPE Insulation M4 Color Code + 3/0AWG Symmetrical Segmented Ground (3 of 4AWG+) Tinned Copper Stranded, Overall Dual Copper Tapes Helically Applied Shield, Black TPE Outer Jacket, 600/1000V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable 1000V WTTC 600V CIC TC SUN RES OIL RES II DIR BUR

## Technical Specifications

### Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems, Exposure to high flex, motion, and abrasion, Hard to reach installation areas
------------------------	--

### Construction Details

#### Conductor

Element	Number of Element	AWG	Stranding	Material	Notes
Conductor(s)	3	3/0	7x7x31x30	TC - Tinned Copper	
Ground	3	4	7x60x30	TC - Tinned Copper	Segmented Grounds

#### Insulation

Element	Material	Thickness	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.057 in (1.4 mm)	Black and Numbered
Ground	No Insulation		

#### Outer Shield Material

Shield Type	Material	Coverage
Helical Tape + Helical Tape	Bare Copper (BC) + Bare Copper (BC)	100% + 100%

#### Outer Jacket Material

Material	Thickness	Nom. Diameter	Ripcord
TPE - Thermoplastic Elastomer	0.083 in (2.1 mm)	1.620 in (41.15 mm)	Yes

Cable Diameter (Nominal):	1.620 in (41.15 mm)
---------------------------	---------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.067 Ohm/1000ft (0.22 Ohm/km)	23 pF/ft (75 pF/m)	42 pF/ft (140 pF/m)	80 Ohm	55%	225 Amps per Conductor at 30°C (per NEC)

#### Voltage

UL Voltage Rating
1000 V (TC, WTTC, UL Flexible Motor Supply Cable), 600 V (C(UL) CIC TC)

### Mechanical Characteristics

#### Temperature

UL Rating	Operating

90°C Dry, 90°C Wet -40°C To +90°C

#### Bend Radius

Stationary Min.	Installation Min.	Flexing Min.
8.1 in (210 mm)	19.4 in (493 mm)	19.4 in (493 mm)

Max. Pull Tension:	7562 lbs (3430 kg)
Bulk Cable Weight:	2373 lbs/1000ft (3531 kg/km)

#### Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1685 UL Loading, FT4, FT4, 1202, 383 Vertical Tray Flame Test (70,000 BTU)
NEC / UL Compliance:	Article 336, TC-ER, WTTTC, XHHW-2, UL Flexible Motor Supply Cable
CEC / C(UL) Compliance:	CIC, TC
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-07-KA070003-MSHA

#### History

Update and Revision:	Revision Number: 0.241 Revision Date: 07-06-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.