



Product: [3109Z](#)

RS485, 4 Pr #22 Str TC, PE Ins, OS+TC Brd, LSZH-TS Jkt, CMG, PLTC

Product Description

RS-485, 4 Pair 22AWG (7x30) Tinned Copper, PE Insulation, Overall Beldfoil®+Tinned Copper Braid(65%) Shield, LSZH-TS Outer Jacket, CMG, PLTC

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	------------------------------------------------------------------------------------------------

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Pair(s)	4	22	7x30	TC - Tinned Copper

Insulation

Element	Material	Thickness	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.023 in	White/Blue Stripe & Blue/White Stripe, White/Orange Stripe & Orange/White Stripe, White/Green Stripe & Green/White Stripe, White/Brown Stripe & Brown/White Stripe	HDPE

Outer Shield Material

Shield Type	Material	Coverage	Drainwire Type
Tape + Braid	Bi-Laminate (Alum+Poly) + Tinned Copper (TC)	100% + 65%	22 AWG (7x30) TC

Outer Jacket Material

Material	Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant, Thermoset)	0.070 in	0.482 in

Cable Diameter (Nominal):	0.482 in
---------------------------	----------

Electrical Characteristics

Electricals

Element	Characteristic Impedence	Nom. Velocity of Prop.
Pair(s)	120 Ohm	78%

High Frequency (Nominal/Typical)

Element
Pair(s)

Voltage

UL Voltage Rating
300 V (CMG, PLTC)

Standards and Compliance

Environmental Suitability:	Sunlight Resistance
NEC / UL Compliance:	Article 725, Article 800, CMG, PLTC
CEC / C(UL) Compliance:	CMG

History

Update and Revision:

Revision Number: 0.122 Revision Date: 03-16-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.