



**Product:** [3111A](#)

Type JX Thermocouple, 1 Pr #20 Sol, PVC Ins Wht, Red, OS, Blk PVC Jkt, 300V PLTC-ER ITC-ER CMG

[Request Sample](#)

**Product Description**

Type JX Thermocouple, 1 Pair 20AWG (Solid) Iron+Constantan, PVC Insulation Wht, Red Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, PLTC-ER ITC-ER CMG AWM 2464 SUN RES DIR BUR

**Technical Specifications**

**Product Overview**

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...),low voltage digital control (24v, ...),Thermocouple, distributed control system (DCS),programmable logic controller (PLC)
------------------------	---

**Construction Details**

**Conductor**

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	20 AWG	Solid	Iron & Constantan

**Insulation**

Element	Material	Nom. Thickness	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.021 in (0.53 mm)	White & Red

**Outer Shield**

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.037 in (0.94 mm)	0.226 in (5.74 mm)	Yes

Overall Cable Diameter (Nominal):	0.226 in (5.74 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Element
Pair(s)

**Voltage**

UL Voltage Rating
300 V (PLTC-ER, CMG, UL AWM 2464), 150 V (ITC-ER)

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
105°C	-30°C to +105°C

**Bend Radius**

Stationary Min.	Installation Min.

2.3 in (58 mm)	2.3 in (58 mm)
----------------	----------------

Max. Pull Tension:	29 lbs (13 kg)
--------------------	----------------

Bulk Cable Weight:	26 lbs/1000ft
--------------------	---------------

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
----------------------------	--

Flammability / Reaction to Fire:	UL1685 (FT4 Loading), FT4, 1202
----------------------------------	---------------------------------

NEC / UL Compliance:	Article 725, Article 727, Article 800, CMG, PLTC-ER, ITC-ER
----------------------	---

AWM Compliance:	AWM 2464
-----------------	----------

CEC / C(UL) Compliance:	CMG
-------------------------	-----

European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
--------------------------------	---

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

Other Standard Compliance(s):	ISA MC 96.1-1982 Type JX
-------------------------------	--------------------------

## Product Notes

Notes:	Constantan is a Hoskins Manufacturing Company trademark.
--------	--

## History

Update and Revision:	Revision Number: 0.362 Revision Date: 04-08-2022
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
3111A 0101000	Black	Reel	1,000 ft	612825141860
3111A 0105000	Black	Reel	5,000 ft	612825141877

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.