



**Product:** [3115A](#)

Type JX Thermocouple, 2 Pr #20+22 Sol, PVC Ins Wht, Red, IS/OS, Blk PVC Jkt, 300V PLTC-ER ITC-ER CMG

[Request Sample](#)

**Product Description**

Type JX Thermocouple, 2 Pair 20+22AWG (Solid) Iron+Constantan, PVC Insulation Wht, Red Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, PLTC-ER ITC-ER CMG AWM 2464 SUN RES DIR BUR

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

Element	AWG	Stranding	Material	Nominal Diameter	No. of Conductors	No. of Pairs
Pair(s)	20	Solid	Iron & Constantan			2
Comm		7x30	BC - Bare Copper	.066 in	1	

Conductor Count: 5

**Insulation**

Element	Material	Nominal Wall Thickness
Pair(s)	PVC - Polyvinyl Chloride	0.021 in
Comm	PVC - Polyvinyl Chloride	0.019 in

**Color Chart**

Number	Color
Constantan	Red Numbered 1
Iron	White Numbered 1
Constantan	Red Numbered 2
Iron	White Numbered 2
Communication Wire	Orange

**Inner Shield Material**

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22	7x30

**Outer Shield Material**

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

**Outer Jacket Material**

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.328 in	0.042 in	Yes

**Construction and Dimensions**

**Stranding**

Twists
4.8 twist/ft

**Electrical Characteristics**

## Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Outer Shield DCR
10.6 Ohm/1000ft	6.8 Ohm/1000ft

## Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

## Mechanical Characteristics

Bulk Cable Weight:	48.5 lbs/1000ft
Max. Pull Tension:	55.5 lbs
Min Bend Radius/Minor Axis:	3.3 in

## Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMG, ITC, PLTC
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	2464
ANSI Compliance:	MC 96.1-1982 Type JX
Other Compliance:	ISA MC 96.1-1982 Type JX

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
3115A 0105000	Black	Reel	5,000 ft	612825141952

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

## Product Notes

Notes:	Iron & Constantan = ""Constantan is a Hoskins Manufacturing Company trademark.""
--------	--

## History

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.