



Product: [29552C](#)

VFD, 3C #10 Str BC XLPE Ins + #10 Symm. Seg. Gnd (3 of #14) Str BC, CTS, Bk PVC Jkt, 1000V CSA TC C22.2 #230 C22.2 #38

[Request Sample](#)

### Product Description

Belden Basics CSA VFD, 3 Conductor 10AWG (7x18) Bare Copper XLPE Insulation M4 Color Code + 10AWG Symmetrical Segmented Ground (3 of 14AWG) Bare Copper Stranded, Overall Dual Copper Tapes Helically Applied Shield, Black PVC Outer Jacket, 1000V CSA TC C22.2 #230 C22.2 #38 SUN RES DIR BUR Oil Resistance

### Technical Specifications

#### Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems; Specific ratings for applications in Canada
------------------------	--

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material	Notes
Conductor(s)	3	10 AWG	7x18	BC - Bare Copper	
Ground	3	14 AWG	7x22	BC - Bare Copper	Segmented Grounds

##### Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.045 in (1.1 mm)	Black and Numbered
Ground	No Insulation		

##### Outer Shield

Shield Type	Material	Coverage
Helical Tape	Bare Copper (BC)	100%
Helical Tape	Bare Copper (BC)	100%

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.073 in (1.9 mm)	0.615 in (15.6 mm)	Yes

Overall Cable Diameter (Nominal):	0.615 in (15.6 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.895 Ohm/1000ft (2.94 Ohm/km)	33 pF/ft (110 pF/m)	60 pF/ft (200 pF/m)	56 Ohm	55%	40 Amps per Conductor at 30°C

##### Voltage

<b>UL Voltage Rating</b>
1000 V (CSA TC)

#### Mechanical Characteristics

##### Temperature

<b>Operating</b>
------------------

-40°C To 90°C

#### Bend Radius

Stationary Min.	Installation Min.
7.4 in (190 mm)	7.4 in (190 mm)

Max. Pull Tension:	553 lbs (251 kg)
Bulk Cable Weight:	285 lbs/1000ft (424 kg/km)

#### Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	1202, 383 Vertical Tray Flame Test (70,000 BTU)
CEC / C(UL) Compliance:	TC, RW90, C22.2 #230, #38
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

#### History

Update and Revision:	Revision Number: 0.357 Revision Date: 04-11-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.