



Product: [31516](#)

Lead Wire, #16 Str TC, Neoprene Ins, AWM 3044

[Request Sample](#)

### Product Description

Low Temp Rubber Lead Wire, 16AWG (26x30) Tinned Copper, Neoprene Insulation, AWM 3044 CSA TYPE CL902300V 90C

### Technical Specifications

#### Product Overview

Suitable Applications:	internal wiring of appliances, oil resistance applications, motor lead systems
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Conductors
16	26x30	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

##### Insulation

Material	Nominal Wall Thickness
Neoprene	0.032 in

#### Electrical Characteristics

##### Voltage

UL Voltage Rating
300 V RMS

#### Temperature Range

Non-UL Temp Rating:	90°C
UL Temp Rating:	90°C

#### Mechanical Characteristics

Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C) ~ 8 Hours @ 325°F (163°C) ~ 15 Minutes @ 450°F (232°C)
Bulk Cable Weight:	15 lbs/1000ft
Min. Bend Radius/Minor Axis:	0.49 in

#### Standards

UL AWM Style Compliance:	AWM 3044
CSA Rating:	300 V RMS, 90°C
CSA Type:	CL902

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes

EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

UL voltage rating:	300 V RMS
--------------------	-----------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
31516 010500	Black	Reel	500 ft	612825142300
31516 0105000	Black	Reel	5,000 ft	612825142317
31516 0055000	Green, Dark	Reel	5,000 ft	612825142287
31516 002500	Red	Reel	500 ft	612825142263
31516 0025000	Red	Reel	5,000 ft	612825142270
31516 009500	White	Reel	500 ft	612825142294

Footnote:	F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'. C - CRATE REEL PUT-UP. I - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'. U - TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10,000' PER COLOR COMBINATION. (SEE TOPCOAT ADDER TABLE), Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

## History

Update and Revision:	Revision Number: 0.395 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.