



**Product:** [34400](#)

Lead Wire, #2/0 Str TC, CSPE Ins, AWM 3193

[Request Sample](#)

**Product Description**

Low Temp Rubber Lead Wire, 2/0AWG (504x26) Tinned Copper, CSPE Insulation, AWM 3193 CSA TYPE CL1052 600V 105C

**Technical Specifications**

**Product Overview**

Suitable Applications:	Class 130(B) motor lead systems, internal wiring of appliances, oil resistance applications
------------------------	---

**Construction Details**

**Conductor**

Element	Number of Element	Size	Stranding	Material
Conductor(s)	1	2/0 AWG	504x26	TC - Tinned Copper

**Insulation**

Material	Nom. Thickness	Nom. Insulation Diameter
CSPE - Chlorosulphonated Polyethylene	0.091 in (2.3 mm)	0.653 in (16.6 mm)

Overall Cable Diameter (Nominal):	0.653 in (16.6 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Nom. Conductor DCR	Max. Current
0.0913 Ohm/1000ft	366.4 Amps per Conductor at 30°C

**Voltage**

UL Voltage Rating	Voltage Rating
600 V (AWM 3193)	300 V (CSA CL-1052)

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
105°C	-30°C To +105°C

**Bend Radius**

Stationary Min.	Installation Min.
6.53 in (166 mm)	6.53 in (166 mm)

Max. Pull Tension:	1606 lbs (728.5 kg)
Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C)
Bulk Cable Weight:	524 lbs/1000ft

**Standards and Compliance**

Environmental Suitability:	Indoor, Outdoor, Oil Resistance
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	Horizontal flame

AWM Compliance:	AWM 3193
CEC / C(UL) Compliance:	CL-1052
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

### Product Notes

Notes:	Exact strand count may vary. Separator tape over the conductor.
--------	---

### History

Update and Revision:	Revision Number: 0.425 Revision Date: 06-30-2022
----------------------	--

### Part Numbers

#### Variants

Item #	Color	Putup Type	Length	UPC
34400 010100	Black	Reel	100 ft	612825143635
34400 010250	Black	Reel	250 ft	612825143642

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.