



Part Number: 3084F

DeviceBus®, 2 Pr #22+24 Str TC, PVC&PO Ins, IS+OA TC Brd, PVC Jkt, High Flex

[🛒 Request Sample](#)

Product Description

DeviceBus® for ODVA DeviceNet™, 2 Pair 22+24AWG (154x44+105x44) Tinned Copper, PVC&PO Insulation, Individual Beldfoil® & OA Tinned Copper Braid(65%) Shield, PVC Outer Jacket, High Flex

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	155x44	TC - Tinned Copper	1
24	105x44	TC - Tinned Copper	1

Conductor Count: 4

Insulation

Element	Material	Nominal Wall Thickness
22	PVC - Polyvinyl Chloride	0.016 in
24	FPE - Foamed Polyethylene	0.026 in

Color Chart

Number	Color
22 AWG Pair	Red & Black
24 AWG Pair	Blue & White

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	26x36

Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	65 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.275 in	0.036 in

Electrical Characteristics

Conductor DCR

Element	Max. Conductor DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
22 AWG	17.5 Ohm/1000ft	Max 17.5 Ohm/1000ft	3.2 Ohm/1000ft
24 AWG	28 Ohm/100m		

Capacitance

Element	Nom. Capacitance Conductor to Conductor
24 AWG Pair	
	12.0 pF/ft

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Impedance Description
100 Ohm	24 AWG Pair
120 Ohm	

Delay

Max. Delay	Max. Delay Description	Nominal Delay	Nominal Velocity of Propagation (VP) [%]	Nominal Velocity of Propagation (VP) Description
1.36 ns/ft	24 AWG Pair			24 AWG Pair
		1.36 ns/ft	75 %	

High Freq

Element	Frequency [MHz]
24 AWG Pair Only	0.125 MHz
	0.5 MHz
	1 MHz

Current

Max. Recommended Current [A]
4 Amps per conductor @ 24 V per NEC CL2 (Power Pair)
4 Amps per conductor @ 24 V per NEC CL2 (Power Pair)

Voltage

UL Description	UL Voltage Rating
CL2, CMG	300 V RMS
C(UL) AWM	

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Oil Resistance:	Yes
Bulk Cable Weight:	41 lbs/1000ft
Max Recommended Pulling Tension:	65 lbs
Min Bend Radius/Minor Axis:	2.75 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CL2, CMG
CEC/C(UL) Specification:	CMG
CSA AWM Specification:	AWM I/II A
Other Specification:	ODVA Class 2 Thin

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Oil Resistance:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
3084F T5U1000	Gray T5U	612825140931	1,000 ft	C
3084F T5U2000	Gray T5U	612825140948	2,000 ft	C
3084F T5U500	Gray T5U	612825140955	500 ft	C N
3084F T5U5000	Gray T5U	612825140962	5,000 ft	C Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	N - FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Product Notes

Notes:	Hi-Flex. Thin. Flex Test Results: ""S-Bend"" Flex Test - 4"" Diameter Wheels, 2 lbs. tension: 150, 000 Cycles Averaged. +/-90 Degree Flex Test: 2"" Diameter, 2 lbs. tension - 8500 Cycles Averaged. Flex tests were conducted at less than the recommended cable minimum bend radius. Actual cable performance will depend on the individual application. Meter marks on jacket to aid users in installation.
--------	--

History

Update and Revision:	Revision Number: 0.332 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.