



**Product:** [3480C](#) 

Communication and Control, 10PR #28, Str, PVC, Semi Rigid, 300 V, AWM/STYLE 2464 80C, CL2 75C, VW-1, CSA CMG, CSA FT4

## Product Description

Communication and Control, 10 Pair 28 AWG (7/36) TC - Tinned Copper, PVC, Semi Rigid Insulation, Overall Aluminum/Polyester Shield, Slate PVC Outer Jacket, AWM/STYLE 2464 80C, CL2 75C, VW-1, CSA CMG, CSA FT4 CMG, FT4 UL FT4, VW-1; CSA FT4

## Technical Specifications

### Product Overview

Suitable Applications:	Industrial control systems, raceways, cable trays, and ducts; instrumentation and control circuits; analog and digital signals (4–20 mA, 0–10 V); PLC and DCS systems; sensors, encoders, solenoids, valves, actuators, and positioners.
------------------------	--

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	10	28 AWG	7x36	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.010 in (0.25 mm)	0.035 in (0.89 mm)	Black-Red, Black-White, Black-Green, Black-Blue, Black-Brown, Black-Yellow, Black-Orange, Red-Green, Red-White, Red-Blue

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	28 AWG (7x36) TC
Braid	Tinned Copper (TC)	65%	

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.332 in (8.43 mm)

Overall Cable Diameter (Nominal):	0.332 in (8.43 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Inductance
Pair(s)	21 pF/ft (69 pF/m)	380 pF/ft (1200 pF/m)	0.22 µH/ft (0.72 µH/m)

Nom Outer Shield DCR:	28 Ohm/1000ft (92 Ohm/km)
-----------------------	---------------------------

#### Voltage

UL Voltage Rating
300 V (CMG, AWM 2464), 150 V (CL2)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
80°C	-20°C To +80°C

## Bend Radius

### Stationary Min.

3.3 in (84 mm)

Max. Pull Tension: 53 lbs (24 kg)

## Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Product Notes

Notes: Alpha Wire -\* P/N 3480C 10PR 28 AWG SHIELDED 75C (UL) TYPE CL2 OR AWM 2464 --- LLXXXXXX CSA TYPE CMG FT4 CE ROHS

## History

Update and Revision: Revision Number: 0.26 Revision Date: 06-30-2026

## Part Numbers

### Variants

Item #	Color	Putup Type	Length
3480C SL005	Black and Red	Reel	100 ft
3480C SL002	Black and Red	Reel	500 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.