



Product: [34G1.0](#)

MachFlex™ 350YY, 33C+1G 1 mm² Str BC, PVC Ins, PVC Jkt

Product Description

MachFlex™ 350YY Control VDE Certified, 33 Conductor + 1 Ground 1 mm² Stranded Bare Copper, PVC Insulation, PVC Jacket

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Applicable for occasional flexing or fixed installation connecting precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more. |
|------------------------|--|

Construction Details

Conductor

| Element | No. of Elements | Size | Stranding | Stranding Class | Material |
|--------------|-----------------|-------------------|-----------|-----------------|------------------|
| Conductor(s) | 33 | 1 mm ² | Stranded | Class 5 | BC - Bare Copper |
| Ground | 1 | 1 mm ² | Stranded | Class 5 | BC - Bare Copper |

Insulation

| Element | Material | Color Code |
|--------------|--------------------------|--|
| Conductor(s) | PVC - Polyvinyl Chloride | Black #1, Black #2, Black #3, Black #4, Black #5, Black #6, Black #7, Black #8, Black #9, Black #10, Black #11, Black #12, Black #13, Black #14, Black #15, Black #16, Black #17, Black #18, Black #19, Black #20, Black #21, Black #22, Black #23, Black #24, Black #25, Black #26, Black #27, Black #28, Black #29, Black #30, Black #31, Black #32, Black #33 |
| Ground | PVC - Polyvinyl Chloride | Yellow/Green |

Outer Jacket

| Material | |
|-----------------------------------|--------------------|
| PVC - Polyvinyl Chloride | |
| Overall Cable Diameter (Nominal): | 17.7 mm (0.697 in) |

Electrical Characteristics

Voltage

| Voltage Rating |
|------------------------------------|
| 300/500 V (Max. Operating Voltage) |

Mechanical Characteristics

Temperature

| Operating | Installation |
|-------------------------------------|------------------------------------|
| -15°C to +70°C(Occasional movement) | -40°C to +80°C(Fixed installation) |

Bend Radius

| Installation Min. | Flexing Min. |
|-------------------|------------------|
| 70.8 mm (2.79 in) | 177 mm (6.97 in) |

| | |
|--------------------|----------------------------|
| Bulk Cable Weight: | 534 kg/km (359 lbs/1000ft) |
|--------------------|----------------------------|

Standards and Compliance

| | |
|---------------------------------------|---|
| Environmental Suitability: | Indoor, Outdoor, Oil Resistance - EN 50290-2-22 (TM54) |
| Flammability / Reaction to Fire: | IEC 60332-1-2, DIN VDE 048233212, DIN EN 6033212 |
| Third Party Performance Verification: | VDE Certification No. 40041970, VDE Registration No. 8770 |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |
| Other Standard Compliance(s): | VDE 0285-525-2-51, IEC 60227-5, EN 50525-2-51 |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.68 Revision Date: 03-19-2024 |
|----------------------|---|

Part Numbers

Variants

| Item # | Color | Length |
|----------------|-----------------|--------|
| 34G1.0 010100M | Black, RAL 9004 | 100 m |
| 34G1.0 010200M | Black, RAL 9004 | 200 m |
| 34G1.0 010300M | Black, RAL 9004 | 300 m |
| 34G1.0 G8U100M | Gray, RAL 7001 | 100 m |
| 34G1.0 G8U200M | Gray, RAL 7001 | 200 m |
| 34G1.0 G8U300M | Gray, RAL 7001 | 300 m |

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.