



Product: [3085A](#)

DeviceBus®, 2 Pr #22+24 Str TC, PVC+FPE Ins, IS+OA TC Brd, CPE Jkt, CMG, CL2

[Request Sample](#)

Product Description

DeviceBus® for ODVA DeviceNet™, 2 Pair 22+24AWG (19x34+19x36) Tinned Copper, PVC+Foam PE Insulation, Individual Beldfoil® & OA Tinned Copper Braid(65%) Shield, CPE Outer Jacket, CMG, CL2

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, ODVA device-level communication, used with CIP (common Industrial Protocol) for control, configuration, and data collection between devices, such as sensors and actuators, and higher level devices such as PLC, and PC in industrial automation, bus topology, etc.
------------------------	--

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Power Pair(s)	1	22	19x34	TC - Tinned Copper
Data Pair(s)	1	24	19x36	TC - Tinned Copper

Insulation

Element	Material	Thickness	Color Code
Power Pair(s)	PVC - Polyvinyl Chloride	0.021 in	Red & Black
Data Pair(s)	PE - Polyethylene (Foam)	0.026 in	Blue & White

Inner Shield Material

Element	Shield Type	Material	Coverage
Power Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%
Data Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%

Outer Shield Material

Shield Type	Material	Coverage	Drainwire Type
Braid	Tinned Copper (TC)	65%	22 AWG (19x34) TC

Outer Jacket Material

Material	Thickness	Nom. Diameter
CPE - Chlorinated Polyethylene	0.033 in	0.280 in

Cable Diameter (Nominal):	0.280 in
---------------------------	----------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Power Pair(s)	17.5 Ohm/1000ft				4 Amps Per Conductor at 24 V (per NEC CL2) (Power Pair)
Data Pair(s)		12.0 pF/ft	120 Ohm	75%	4 Amps Per Conductor at 24 V (per NEC CL2) (Power Pair)

Nom Outer Shield DCR:	3.2 Ohm/1000ft
-----------------------	----------------

High Freq

Element	Frequency [MHz]	Max. Insertion Loss (Attenuation)
---------	-----------------	-----------------------------------

Data Pair(s)	0.125 MHz	.29 dB/100ft
	0.5 MHz	0.5 dB/100ft
	1 MHz	0.7 dB/100ft

Voltage

UL Voltage Rating
300 V (CMG)

Mechanical Characteristics

Temperature

UL Rating	Operating
75°C	-30°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
2.75 in	2.75 in

Max. Pull Tension:	65 lbs
Bulk Cable Weight:	46 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Sunlight Resistance
Flammability / Fire Resistance:	UL1685 FT4 Loading, FT4, 1202, IEC 60332-1-2
NEC / UL Compliance:	Article 725, Article 800, CL2, CMG
CEC / C(UL) Compliance:	CMG
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ODVA Class 2 Thin

Product Notes

Notes:	Thin. Meter marks on jacket to aid users in installation. ODVA Devicenet is an Open DeviceNet Vendor Association, Inc. trademark.
--------	---

History

Update and Revision:	Revision Number: 0.397 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.