



**Product:** [3092T](#)

ControlBus™, Coax RG6, #18 Sol BCCS, PO Ins, QUAD AL Shld, LSZH Jkt, CMG

[Request Sample](#)

### Product Description

ControlBus™, Coax RG6 18AWG (Solid) Bare Copper Covered Steel, PO Insulation, Overall Duofoil®+ Aluminum Braid(60%)+Overall Duofoil®+Aluminum Braid(40%) Shield, LSZH Outer Jacket, CMG

### Technical Specifications

#### Product Overview

Suitable Applications:	harsh environment, factory automation, ControlNet™, Modbus II, Industrial Coax, Belden ControlNet cables provide maximum signal integrity and run length exceeding the high-speed, time-critical requirements necessary for ControlNet factory floor applications
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BCCS - Bare Copper Covered Steel	0.040 in	1

Conductor Count: 1

##### Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.180 in

##### Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
Braid	2	Aluminum		60%
Tape	3	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	4	Aluminum		60%

##### Outer Jacket

Material	Nominal Diameter
PE - Polyethylene	0.3 in

Table Notes: Flame Retardant

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Outer Conductor DCR
28 Ohm/1000ft	3.6 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

##### Inductance

Nominal Inductance
0.097 µH/ft

## Impedance

### Nominal Characteristic Impedance

75 Ohm

## Return Loss (RL)

### Frequency [MHz] | Min. Structural Return Loss (SRL)

5-50 MHz | 23 dB

## High Frequency (Nominal/Typical)

### Frequency [MHz] | Nom. Insertion Loss

1 MHz | 0.35 dB/100ft

2 MHz | 0.38 dB/100ft

5 MHz | 0.45 dB/100ft

10 MHz | 0.59 dB/100ft

20 MHz | 0.86 dB/100ft

50 MHz | 1.37 dB/100ft

100 MHz | 1.97 dB/100ft

200 MHz | 2.82 dB/100ft

300 MHz | 3.48 dB/100ft

400 MHz | 4.04 dB/100ft

## Delay

### Nominal Delay | Nominal Velocity of Propagation (VP) [%]

1.25 ns/ft | 83%

## Voltage

### UL Voltage Rating

300 V RMS

## Temperature Range

UL Temp Rating: 75°C

Operating Temperature Range: -20°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight: 35 lbs/1000ft

Max. Pull Tension: 162 lbs

Min. Bend Radius/Minor Axis: 3.0 in

## Standards

NEC/(UL) Compliance: CL2, CMG

CEC/C(UL) Compliance: CMG

RG Type: 6

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/11/EC (BFR): Yes

EU Directive 2011/65/EU (RoHS 2): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU (RoHS 2 amendment): Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

## Flammability, LS0H, Toxicity Testing

IEC Flammability: IEC 60332-3-22

IEEE Flammability: 1202

UL voltage rating: 300 V RMS

## Related Part Numbers

## Variants

Item #	Color	UPC
3092T 0105000	Black	612825141433

## History

Update and Revision:	Revision Number: 0.330 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.