



REPRESENTATIVE IMAGE

**Product:** [3093A](#)

ControlBus™, Coax RG-6, #18 Sol BCCS, FFEP Ins, QUAD AL Shld, PVDF Jkt, CMP High Temp 150C

[Request Sample](#)

**Product Description**

Coax RG-6 18 AWG (Solid) Bare Copper Covered Steel, Foam FEP Insulation, Overall Duobond® II+ Aluminum Braid(60%)+Duofoil®+Aluminum Braid(40%) Shield, PVDF Outer Jacket, CMP High Temp 150C

**Technical Specifications**

**Product Overview**

Suitable Applications:	harsh environment, factory automation, ControlNet™, Modbus II, Industrial Coax, Belden ControlNet cables provide maximum signal integrity and run length exceeding the high-speed, time-critical requirements necessary for ControlNet factory floor applications
------------------------	---

**Construction Details**

RG Type:	6
----------	---

**Conductor**

AWG	Stranding	Nom. Diameter	Material
18	Solid	0.040 in	BCCS - Bare Copper Covered Steel

**Insulation**

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.170 in

**Outer Shield Material**

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Aluminum		60%
3	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
4	Braid	Aluminum		40%

**Outer Jacket Material**

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.274 in

**Electrical Characteristics**

**Return Loss (RL)**

Frequency [MHz]	Min. Structural Return Loss [dB]
5 - 50 MHz	23 dB

**Attenuation**

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.36 dB/100ft
2 MHz	0.38 dB/100ft
5 MHz	0.5 dB/100ft
10 MHz	0.65 dB/100ft
20 MHz	0.95 dB/100ft
50 MHz	1.5 dB/100ft
100 MHz	2.12 dB/100ft

200 MHz	2.99 dB/100ft
300 MHz	3.66 dB/100ft
400 MHz	4.23 dB/100ft

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedence	Nom. Velocity
28 Ohm/1000ft	2.6 Ohm/1000ft	16.5 pF/ft	75 Ohm	82%

#### Voltage

UL Voltage Rating
300 V (CMP)

## Mechanical Characteristics

#### Temperature

UL Rating	Operating
150°C	-20°C to +150°C

#### Bend Radius

Installation Min.
2.75 in

Bulk Cable Weight:	36 lbs/1000ft
Max. Pull Tension:	118 lbs

## Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Outdoor, Burial
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	NFPA 262
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	3092A

## Product Notes

Notes:	Blue available as standard in 1000-ft put-up only. Suitable for Outdoor and Direct Burial applications.
--------	---

## History

Update and Revision:	Revision Number: 0.373 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.