



Product: [3094A](#)

ControlBus™, Coax RG-11, #14 Sol BCCS, FPE Ins, QUAD AL Shld, PVC Jkt, CMR

[Request Sample](#)

Product Description

Coax RG-11 14AWG (Solid) Bare Copper Covered Steel, Foam PE Insulation, Overall Duobond® II+ Aluminum Braid(60%)+Duofoil®+Aluminum Braid(40%) Shield, PVC Outer Jacket, CMR

Technical Specifications

Product Overview

Suitable Applications:	Harsh environment, factory automation, ControlNet™, Modbus II, Industrial Coax, Belden ControlNet cables provide maximum signal integrity and run length exceeding the high-speed, time-critical requirements necessary for ControlNet factory floor applications
------------------------	---

Construction Details

RG Type:	11
----------	----

Conductor

Size	Stranding	Nom. Diameter	Material
14 AWG	Solid	0.064 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PE - Polyethylene (Foam)	0.280 in (7.11 mm)	White	Gas Injected

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Aluminum		60%
3	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
4	Braid	Aluminum		40%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.407 in (10.3 mm)
Overall Cable Diameter (Nominal):	0.407 in (10.3 mm)

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Structural Return Loss
5 - 400 MHz	20 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.16 dB/100ft
2 MHz	0.18 dB/100ft
5 MHz	0.26 dB/100ft
10 MHz	0.38 dB/100ft
20 MHz	0.55 dB/100ft

50 MHz	0.83 dB/100ft
100 MHz	1.17 dB/100ft
200 MHz	1.60 dB/100ft
300 MHz	1.99 dB/100ft
400 MHz	2.30 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
11.5 Ohm/1000ft	1.8 Ohm/1000ft (5.9 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating
300 V (CMR, CMG)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-30°C to 75°C

Bend Radius

Installation Min.
4 in (100 mm)

Max. Pull Tension:	234 lbs (106 kg)
Bulk Cable Weight:	60 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Outdoor, Sunlight Resistance, Aerial - When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1666 Riser
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMR, CL2R
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	3095A

Product Notes

Notes:	Tap marks every 2.6 meters to aid users in installation.
--------	--

History

Update and Revision:	Revision Number: 0.513 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
3094A F2V500	Gray, DEC	Reel	500 ft	612825141525	
3094A F2V1000	Gray, DEC	Reel	1,000 ft	612825141501	
3094A F2V2000	Gray, DEC	Reel	2,000 ft	612825141518	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

