



Product: [35618](#)

Lead Wire, #18 Str TC, XLPO Ins, AWM 3173

[Request Sample](#)

Product Description

Rubber Lead Wire, 18AWG (16x30) Tinned Copper, XLPO Insulation, AWM 3173 CSA TYPE CL1251 600V 125C

Technical Specifications

UL voltage rating:	600 V RMS
--------------------	-----------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
35618 010500	Black	Reel	500 ft	612825145233
35618 0105000	Black	Reel	5,000 ft	612825145240
35618 0135000	Blue, Dark	Reel	5,000 ft	612825145264
35618 0065000	Blue, Light	Reel	5,000 ft	612825145196
35618 0015000	Brown	Reel	5,000 ft	612825145127
35618 0085000	Gray	Reel	5,000 ft	612825145219
35618 0055000	Green, Dark	Reel	5,000 ft	612825145189
35618 0035000	Orange	Reel	5,000 ft	612825145158
35618 0125000	Pink	Reel	5,000 ft	612825145257
35618 002500	Red	Reel	500 ft	612825145134
35618 0025000	Red	Reel	5,000 ft	612825145141
35618 0075000	Violet	Reel	5,000 ft	612825145202
35618 0095000	White	Reel	5,000 ft	612825145226
35618 004500	Yellow	Reel	500 ft	612825145165
35618 0045000	Yellow	Reel	5,000 ft	612825145172

Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
Footnote:	F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.
Footnote:	C - CRATE REEL PUT-UP.
Footnote:	I - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'.
Footnote:	U - TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10,000' PER COLOR COMBINATION. (SEE TOPCOAT ADDER TABLE)

History

Update and Revision:	Revision Number: 0.302 Revision Date: 02-16-2021
----------------------	--

Product Overview

Suitable Applications:	Class 130(B) motor lead systems, internal wiring of appliances
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
18	16x30	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Diameter	Nominal Wall Thickness	Min. Average Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.109 in	0.032 in	0.03 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.5 Ohm/1000ft

Current

Element	Max. Recommended Current [A]
Single conductor in free air @ ambient 30C	Single conductor in free air @ 30°C: 22 A

Voltage

UL Voltage Rating
600 V RMS

Temperature Range

UL Temp Rating:	125°C
-----------------	-------

Mechanical Characteristics

Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C) ~ 12 Hours @ 325°F (163°C) ~ 8 Hours @ 350°F (177°C)
Bulk Cable Weight:	10 lbs/1000ft
Min Bend Radius/Minor Axis:	0.44 in

Standards

UL AWM Style Compliance:	UL AWM Style 3173
CSA Rating:	600 V, 125°C
CSA Type:	CL1251

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-07-01
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.