



Part Number: 3613

CAT6+ Horizontal, 4pr, UTP, LS-PVC Jkt, CMP

Product Description

CAT6+ (400MHz), 4-Pair, U/UTP-unshielded, Plenum-CMP, Premise Horizontal cable, 23 AWG solid bare copper conductors, dual FRPO/FEP insulation, patented X-spline Center Member, ripcord, Flammarrest® PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Plenum
Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material
FRPO/FEP - Flame Retardant Polyolefin/Fluorinated Ethylene Propylene

Bonded-Pair:	N/A
--------------	-----

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness	Ripcord	Separator Material
LS PVC - Low Smoke Polyvinyl Chloride	Flammarrest®	0.238 in	0.017 in	Yes	Patented X-Spline Center Member

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
77 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	15.5 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
-----------------	------------	-----------------	--	--------------------

100 MHz	537.6 ns/100m	35 ns/100m	70 %	35 ns/100m
---------	---------------	------------	------	------------

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Min. TCL [dB]	Min. ELTCTL [dB]
0.772 MHz	1.8 dB/100m	81.0 dB	81.0 dB	79.2 dB	79.2 dB	75.0 dB	73.0 dB			40.0 dB	37.2 dB
1 MHz	2.0 dB/100m	79.3 dB	79.3 dB	77.3 dB	77.3 dB	72.8 dB	70.8 dB	20.0 dB	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.7 dB/100m	70.3 dB	70.3 dB	66.6 dB	66.6 dB	60.8 dB	58.8 dB	23.0 dB	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	5.2 dB/100m	65.8 dB	65.8 dB	60.6 dB	60.6 dB	54.7 dB	52.7 dB	24.5 dB	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	5.8 dB/100m	64.3 dB	64.3 dB	58.5 dB	58.5 dB	52.8 dB	50.8 dB	25.0 dB	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	7.4 dB/100m	61.2 dB	61.2 dB	53.9 dB	53.9 dB	48.7 dB	46.7 dB	25.0 dB	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	8.3 dB/100m	59.8 dB	59.8 dB	51.5 dB	51.5 dB	46.8 dB	44.8 dB	25.0 dB	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	9.3 dB/100m	58.3 dB	58.3 dB	49.1 dB	49.1 dB	44.8 dB	42.8 dB	24.3 dB	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	10.4 dB/100m	56.9 dB	56.9 dB	46.5 dB	46.5 dB	42.9 dB	40.9 dB	23.6 dB	100 ± 15 Ohm	35.1 dB	
62.5 MHz	15.0 dB/100m	52.4 dB	52.4 dB	37.4 dB	37.4 dB	36.9 dB	34.9 dB	21.5 dB	100 ± 15 Ohm	32.0 dB	
100 MHz	19.3 dB/100m	49.3 dB	49.3 dB	30.0 dB	30.0 dB	32.8 dB	30.8 dB	20.8 dB	100 ± 15 Ohm	30.0 dB	
155 MHz	24.6 dB/100m	46.4 dB	46.4 dB	21.8 dB	21.8 dB	28.9 dB	26.9 dB	19.5 dB	100 ± 22 Ohm	28.1 dB	
200 MHz	28.3 dB/100m	44.8 dB	44.8 dB	16.5 dB	16.5 dB	26.8 dB	24.8 dB	18.7 dB	100 ± 22 Ohm	27.0 dB	
250 MHz	32.1 dB/100m	43.3 dB	43.3 dB	11.2 dB	11.2 dB	24.8 dB	22.8 dB	18.0 dB	100 ± 32 Ohm	26.0 dB	
300 MHz	35.6 dB/100m	42.1 dB	42.1 dB	6.5 dB	6.5 dB	23.3 dB	21.3 dB	17.5 dB	100 ± 32 Ohm		
350 MHz	38.9 dB/100m	41.1 dB	41.1 dB	2.3 dB	2.3 dB	21.9 dB	19.9 dB	17.0 dB	100 ± 32 Ohm		
400 MHz	42.0 dB/100m	38.3 dB	38.3 dB	-3.7 dB	-3.7 dB	20.8 dB	18.8 dB	16.6 dB	100 ± 32 Ohm		
450 MHz	45.0 dB/100m	37.5 dB	37.5 dB			19.7 dB	17.7 dB	16.2 dB	100 ± 32 Ohm		
500 MHz	47.9 dB/100m	36.8 dB	36.8 dB			18.8 dB	16.8 dB	15.9 dB	100 ± 32 Ohm		
550 MHz	50.6 dB/100m	36.2 dB	36.2 dB			18.0 dB	16.0 dB	15.6 dB	100 ± 32 Ohm		
600 MHz	53.3 dB/100m	35.6 dB	35.6 dB			17.2 dB	15.2 dB	15.4 dB	100 ± 32 Ohm		
650 MHz	55.9 dB/100m	35.1 dB	35.1 dB			16.5 dB	14.5 dB	15.1 dB	100 ± 32 Ohm		

Segregation class according EN50174-2: a

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	90°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius During Installation:	2.5 in
Min Bend Radius/Minor Axis:	1.0 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Standards:	C(UL)US CMP 90C OR (UL) CMP-LP (0.6A) OR CL3P-LP (0.6A)
Third Party Performance Verification:	Category 6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2009-04-03
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT6
UL Flammability:	NFPA 262 Plenum (UL 910)
CSA Flammability:	FT6
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	3612
--------------------	------

Variants

Item #	Color	UPC	Length
3613 0101000	Black	612825145967	1,000 ft
3613 0102500	Black	612825145974	2,500 ft
3613 010A1000	Black	612825145943	1,000 ft
3613 010U1000	Black	612825145950	1,000 ft
3613 D151000	Blue	612825145714	1,000 ft
3613 D152500	Blue	612825145721	2,500 ft
3613 D15A1000	Blue	612825335078	1,000 ft
3613 D15U1000	Blue	612825335085	1,000 ft
3613 0081000	Gray	612825145899	1,000 ft
3613 008A1000	Gray	612825145875	1,000 ft
3613 008U1000	Gray	612825145882	1,000 ft
3613 0051000	Green	612825145837	1,000 ft
3613 0052500	Green	612825145844	2,500 ft
3613 005A1000	Green	612825145813	1,000 ft
3613 005U1000	Green	612825145820	1,000 ft
3613 0031000	Orange	612825145769	1,000 ft
3613 003A1000	Orange	612825145745	1,000 ft
3613 003U1000	Orange	612825145752	1,000 ft
3613 012A1000	Pink	612825145981	1,000 ft

3613 007A1000	Purple	612825145851	1,000 ft
3613 007U1000	Purple	612825145868	1,000 ft
3613 002A1000	Red	612825145738	1,000 ft
3613 0091000	White	612825145929	1,000 ft
3613 0092500	White	612825145936	2,500 ft
3613 009A1000	White	612825145905	1,000 ft
3613 009U1000	White	612825145912	1,000 ft
3613 0041000	Yellow	612825145790	1,000 ft
3613 0042500	Yellow	612825145806	2,500 ft
3613 004A1000	Yellow	612825145776	1,000 ft
3613 004U1000	Yellow	612825145783	1,000 ft

Patent: <https://www.belden.com/resources/patents>

Product Notes

Notes: Values above 400 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.

History

Update and Revision: Revision Number: 0.369 Revision Date: 08-22-2019

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.