



**Product:** [31014N](#)

Lead Wire, #14 Str TC, XLPO Ins, UL TYPE SIS

[Request Sample](#)

**Product Description**

Low Temp Rubber Lead Wire, 14AWG (41x30) Tinned Copper, XLPO Insulation, UL TYPE SIS 600V 90C

**Technical Specifications**

**Product Overview**

Suitable Applications:	for wiring switchboards, panelboards , distribution boards
------------------------	--

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
14	41x30	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness
XLPE, XLPO, XLPE (Thermoset)	0.144 in	0.032 in

**Electrical Characteristics**

**Voltage**

<b>UL Voltage Rating</b>
600 V RMS

**Temperature Range**

UL Temp Rating:	90°C
-----------------	------

**Mechanical Characteristics**

Bulk Cable Weight:	20.3 lbs/1000ft
Min. Bend Radius/Minor Axis:	0.58 in

**Standards**

NEC Articles:	Article 310
NEC/(UL) Compliance:	SIS

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65:	Yes

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	600 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
31014N 0082500	Gray	Reel	2,500 ft	612825141570

Footnote:	C - CRATE REEL PUT-UP., U - TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10,000' PER COLOR COMBINATION. (SEE TOPCOAT ADDER TABLE)
-----------	--

## Product Notes

Notes:	Separator material over conductor.
--------	------------------------------------

## History

Update and Revision:	Revision Number: 0.358 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.