



Product: [37114](#)

Lead Wire, #14 Str TC, EPDM Ins, AWM 3340 AWM 3374

Request Sample

### Product Description

Rubber Lead Wire, 14AWG (41x30) Tinned Copper, EPDM Insulation, AWM 3340 AWM 3374 CSA TYPE CL1254 600V 125C FLEX 150C NO FLEX

### Technical Specifications

#### Product Overview

Suitable Applications:	Class 130(B), 155(F) and also in some 180(H) motor lead systems, high temperature, internal wiring of appliances
------------------------	--

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	14 AWG	41x30	TC - Tinned Copper

##### Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
EPDM - Ethylene Propylene Diene Monomer	0.048 in (1.2 mm)	0.169 in (4.29 mm)
Overall Cable Diameter (Nominal):	0.169 in (4.29 mm)	

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Max. Current
2.82 Ohm/1000ft	54.4 Amps per Conductor at 30°C

##### Voltage

UL Voltage Rating
600 V (AWM 3340, AWM 3374)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
150°C	-55°C To +150°C

##### Bend Radius

Stationary Min.	Installation Min.
1.69 in (42.9 mm)	1.69 in (42.9 mm)
Max. Pull Tension:	53.3 lbs (24.2 kg)
Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C) ~ 4 Hours @ 375°F (190°C)
Bulk Cable Weight:	23 lbs/1000ft

#### Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	Horizontal flame

AWM Compliance:	AWM 3340, AWM 3374
CEC / C(UL) Compliance:	CL-1254
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.468 Revision Date: 02-03-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
37114 010500	Black	Reel	500 ft	612825146919	F
37114 0104000	Black	Reel	4,000 ft	612825146902	C I
37114 0105000	Black	Reel	5,000 ft	612825146926	C
37114 002500	Red	Reel	500 ft	612825146896	F
37114 0024000	Red	Reel	4,000 ft	612825146889	C I Z

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.