



**Product:** [38114](#)

UL Type PV Wire, #14 Str TC, XLPO Ins, 2000V PV 90C Dry/Wet

[Request Sample](#)

**Product Description**

UL Type PV Wire, 14AWG (41x30) Tinned Copper, XLPO Insulation, 2000V PV 90C Dry/Wet USE-2 RHW-2 CSA RW90 1000V SUN RES

**Technical Specifications**

**Product Overview**

Suitable Applications:	Interconnection wiring of grounded and ungrounded photovoltaic power systems as described in Section 690.31(A) of the 2008 NEC.
------------------------	---

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
14	41x30	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.237 in	0.078 in
XLP, XLPO, XLPE (Thermoset)		

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
2.4 Ohm/1000ft

**Current**

Element	Max. Recommended Current [A]
Single conductor in free air @ 30 ambient	35 Amps Single Conductor in Free Air

**Voltage**

Non-UL Voltage Rating	UL Description	UL Voltage Rating
600 V	PV, RHW-2	2000 V
	USE-2	600 V RMS

**Temperature Range**

UL Temp Rating:	90°C
Operating Temp Range:	-40°C To +90°C

**Mechanical Characteristics**

Bulk Cable Weight:	34 lbs/1000ft
Max. Pull Tension:	53.5 lbs
Min Bend Radius/Minor Axis:	2.375 in

**Standards**

UL AWM Style Compliance:	PV, USE-2, RHW-2
--------------------------	------------------

CSA Rating:	1000V, 90C
CSA Type:	RW90
Military Compliance:	N/A

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2009-09-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1
UL voltage rating:	2000 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
38114 0105000	Black	Reel	5,000 ft	612825147589

## History

Update and Revision:	Revision Number: 0.293 Revision Date: 07-26-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.